

TEST REPORT

Report No.: SET2014-02585

Product: Switching Power Supply

Model No. : PRO MAX 72W 24V 3A, PRO MAX 72W 12V 6A, PRO MAX
70W 5V 14A

Brand Name: Weidmüller

Applicant: Weidmüller Interface GmbH & Co.,KG

Issued by: CCIC Southern Electronic Product Testing (Shenzhen) Co., Ltd.

Lab Location: Electronic Testing Building, Shahe Road, Xili, Nanshan District,
Shenzhen, 518055, P. R. China

Tel: 86 755 26627338 **Fax:** 86 755 26627238



This test report consists of **17** pages in total. It may be duplicated completely for legal use with the approval of the applicant. It should not be reproduced except in full, without the written approval of our laboratory. The client should not use it to claim product endorsement by CCIC-SET. The test results in the report only apply to the tested sample. The test report shall be invalid without all the signatures of testing engineers, reviewer and approver. Any objections must be raised to CCIC-SET within 15 days since the date when the report is received. It will not be taken into consideration beyond this limit.

Test Report

Product..... Switching Power Supply
Model No. PRO MAX 72W 24V 3A, PRO MAX 72W 12V 6A, PRO MAX 70W 5V 14A
Applicant..... Weidmüller Interface GmbH & Co.,KG
Applicant Address..... Klingenbergstraße 16 32758 Detmold Germany
Manufacturer Weidmüller Interface GmbH & Co.,KG
Manufacturer Address Klingenbergstraße 16 32758 Detmold Germany
Test Standards..... SEMI F47-0706
 <Specification for semiconductor processing equipment voltage sag immunity>
Test Result..... Pass
Tested by Zhu Qi

 Zhu Qi, Mar. 31,2014
Reviewed by Zhang Peng

 Zhang Peng, Mar. 31,2014
Approved by Wu Lian

 Wu Li'an, Mar. 31,2014

