

Teilbare Kabelverschraubung mit Gegenmutter
Separable cable gland with lock nut

CABTITE CGS M20 BK	2584200000
CABTITE CGS M25 BK	2584180000
CABTITE CGS M32 BK	2584160000
CABTITE CGS M40 BK	2584150000
CABTITE CGS M50 BK	2584130000
CABTITE CGS M63 BK	2584120000

Cabtite CGS

Montageanleitung
Installation Instructions


Typ / Type	D [mm]	D [inch]	M [Nm]
CABTITE CGS M20 BK	20 + 0,2	0.79 + 0.008	3,0
CABTITE CGS M25 BK	25 + 0,2	0.98 + 0.008	3,0
CABTITE CGS M32 BK	32 + 0,2	1.26 + 0.008	3,0
CABTITE CGS M40 BK	40 + 0,3	1.57 + 0.012	7,0
CABTITE CGS M50 BK	50 + 0,3	1.97 + 0.012	7,0
CABTITE CGS M63 BK	63 + 0,3	2.48 + 0.012	7,0



