

| IE- FCI- |                 | PWB- |                              | DE-    |                      | OR  |                |
|----------|-----------------|------|------------------------------|--------|----------------------|-----|----------------|
| FCI      | FrontCom insert | PWS- | insert fits to small cut out | US     | US socket            | OR  | Orange version |
| ...      |                 | PWB- | insert fits to big cut out   | DE     | Germany socket       | 10A | 10 A Version   |
|          |                 | ...  |                              | FR     | France socket        | 5V  | 5 V output     |
|          |                 |      |                              | CH     | Suisse socket        | ... |                |
|          |                 |      |                              | GB     | Great Britain socket |     |                |
|          |                 |      |                              | IT     | Italy socket         |     |                |
|          |                 |      |                              | ISR    | Israel socket        |     |                |
|          |                 |      |                              | AU     | Australia socket     |     |                |
|          |                 |      |                              | CN     | China socket         |     |                |
|          |                 |      |                              | IND    | India Socket         |     |                |
|          |                 |      |                              | CZ     | Tech. Rep socket     |     |                |
|          |                 |      |                              | DK     | Denmark socket       |     |                |
|          |                 |      |                              | RCBO   | RCBO device          |     |                |
|          |                 |      |                              | 2USB-A | USB charger          |     |                |
|          |                 |      |                              | ...    |                      |     |                |