


Terminal blocks

Klippon® Connect – SNAP INto the future

The world's first terminal blocks with innovative SNAP IN technology

SNAP IN 

Invented by Weidmüller.




Weidmüller 

The worldwide novelty from the pioneer of industrial connectivity


Klippon® Connect terminal blocks with innovative SNAP IN technology

SNAP IN
Invented by Weidmüller.

Time is money. For this reason, installation work in control cabinet construction must be carried out ever faster, preferably automated. At the same time, the connections should be permanently reliable, safe, and easy to maintain. The new Klippon® Connect terminal blocks with Weidmüller's revolutionary SNAP IN technology meet all these requirements - and are extremely easy to use: stripped fine-stranded conductors just need to be inserted into the connection point, and the connection point snaps shut with a clearly audible click. The conductor is permanently and reliably contacted. To release the connection, press the green pusher. It couldn't be faster or easier.



Your special advantages:



Achieving added value at all stages of panel building

The planning phase is crucial for the success and costeffectiveness of the entire panel building process, and requires the intelligent interplay of digital product data and interconnected engineering tools.

Efficient, easy wiring is key to installation. Our products stand out in this respect with their intuitive handling and

clear design. All terminal functions can be distinguished from each other instantly.

Our Klippon® Connect products feature standardised test points which make automated testing and checking processes possible. In this way, maintenance and testing tasks can be carried out much more safely and faster.



Thanks to the self-releasing connection mechanism, the SNAP IN technology could be connected in record time.



Simple and tool-free connection of flexible and fine-stranded conductors even without a wire end ferrule.



Safety which you could hear! A clear „Click“ sound signals the safe connection.



With the innovative SNAP IN connection, fully automated wiring processes become reality.



Complete terminal strips could be planned digitally via the WMC and ordered - including accessories.



With the „Fast delivery service“, the fully assembled terminal strips are delivered directly to the place of use.

Pioneers in industrial connectivity


Being a pioneer means reinventing yourself time and time again

More than 75 years of experience, several billion connections manufactured and countless hours of development make Weidmüller terminal blocks the safest and most powerful on the market.

1948

SAK-Series

First plastic isolated terminal block



1978

DSK-Series


First terminal block with direct plug in technology



1983

W-Series

First terminal block with self locking clamping yoke technology



1993

Z-Series


First terminal block from Weidmüller with tension clamp technology



2004

P-Series


First terminal block family from Weidmüller with PUSH IN technology



2016

A-Series

First terminal block family with PUSH IN technology with pushers and application products



2021



SNAP IN

S-Series

First terminal block family with SNAP IN technology






Klippon® Connect with SNAP IN technology: For an acceleration of your wiring processes

Simply insert the conductor into the connection point - „Click“ and the reliable connection is ready. The conductor is contacted in the clamping point with a clear „click“. The triggered clamping point is additionally signaled visually by an increased pusher.

Klippon® Connect terminal blocks with SNAP IN technology revolutionize the wiring of control cabinets with their intuitive and simple handling. The pre-loaded clamping point allows direct and tool-free wiring of solid and flexible conductors even without ferrules. The reduction of wire preparation speeds up your wiring times and leads to a more efficient installation process.



Fast, simple and safe – just SNAP IN

Your benefits at a glance



FAST

The new SNAP IN connection technology will take your wiring processes to a whole new level.



SIMPLE

Direct and tool-free wiring without wire end ferrules. Simply insert the stripped conductor into the pre-loaded connection point.




SAVE

The pre-loaded SNAP IN spring connection guarantees a safe and gas-tight connection of the conductor.




READY-TO-ROBOT

Ready-to-robot and optimally equipped for the automation processes of the future.



SNAP IN

- Intuitive and simple handling of SNAP IN technology
- Low mating forces due to simple insertion of the stripped conductor
- Quick and easy connection even without ferrule



PUSH IN

- Tool-free, vibration-proof and gas-tight connection
- Stainless steel spring guarantees a high contact force of the conductor on the current bar
- Simply insert stripped solid conductors into the clamping point



Tension clamp connection

- Separation of electrical and mechanical functions
- Low contact resistance and high corrosion resistance
- Insensitive to vibrations and high conductor pull-out forces



Screw connection

- Gas-tight, vibration-resistant connection
- Excellent contact force
- Suitable for the connection of solid and flexible stranded wires



SNAP IN – The Challenge:
A different kind of product test.

Take part and experience innovation in action!

Klippon® Connect with SNAP IN technology: For simple and intuitive operation

The new connection is as simple in principle as it is to use: The terminal blocks are delivered with pre-loaded spring. Stripped wires could be easily and safely inserted into the clamping point without further preparation. The conductor is contacted in the clamping point with a clear „Click“. And it's just as fast the other way round. By pressing the pusher, the conductor can be quickly and easily released at any time and the clamping point pre-loaded again.



Step 1

The terminal blocks are delivered with pre-loaded spring. The status of the pre-loaded terminal block is signaled by the height position of the pusher.



Step 2

Stripped wires could be easily and safely inserted into the clamping point without further preparation.



Step 3

The conductor is contacted in the clamping point with a clear „Click“. The triggered clamping point is additionally signaled visually by an increased pusher.



Step 4



By pressing the pusher until the „second click“, the conductor can be easily released and the clamping point pre-loaded again.

Klippon® Connect with SNAP IN technology: For guaranteed and safe conductor connection

The pre-tensioned contact point technology allows flexible conductors without wire-end ferrules to be plugged in directly with low insert force. A special tool is not required.

Once the conductor is inserted correctly and deeply enough into the contact point, the contact point is reliably triggered. Reliable contacting of the conductor guarantees that the wire connection is protected against vibration, gas-tight and stable for the long-term.

In addition to the audible „Click“, the pusher is elevated to indicate the secure connection. Klippon® Connect rail-mounted terminal blocks with innovative SNAP IN technology ensure maximum process reliability.



SNAP IN – simply explained!

Get to know the quick handling of the innovative SNAP IN technology!

Klippon® Connect with SNAP IN technology: For the automation of the future

Increasing automation in panel building is posing new requirements for future terminal blocks. These requirements were already taken into account during the development phase. The optimized design supports a robot-assisted assembly. Pre-assembled markers in combination with the Klippon® Automated RailLaser, automated marking of the terminal strip. The open connection point of the S-series – „ready to wire“ - also enables robot-assisted wiring of terminal strip.

Automated snapping on and cutting to size with the Klippon® Automated RailAssembler and the Klippon® Automated RailCutter

With automated production processes, errors can be avoided, workflows accelerated, and costs reduced. This works best with solutions based on each other and thought out down to the last detail. The contours of the new SNAP IN S-Series terminal blocks have been designed to be easily gripped and mounted by industrial robots. This means there is no obstacle to automated assembly today.

The RailCutter is an extension of the Klippon® Automated RailAssembler and the only fully automatic machine that cuts mounting rails to size. The Klippon® Automated RailCutter cuts mounting rails to size and labels them automatically.



- Klippon® Automated RailAssembler and RailCutter**
- Up to 60 % time saving in terminal block assembly (or significantly more considering the unmanned operation of up to 7 hours)
 - Avoidance of incorrect assembly thanks to data consistency between eCAD programs and Weidmüller Configurator (WMC)
 - Easy handling due to universal magazines
 - Cost-efficient in the long term, high flexibility and data consistency

Ordering data	
Type	Order No.
RAILASSEMBLER	2738690000
RAILASSEMBLER INCL. RAILCUTTER	2994740000
RAILCUTTER RETROFIT*	2994760000
RAILASSEMBLER INCL. RAILCUTTER US VERSION	2994750000
RAILCUTTER STANDALONE US VERSION	2994780000


*Retrofitting to existing RailAssembler



Take a closer look at the Klippon® Automated RailAssembler.
Just scan the QR code and watch the video.

Automated marking with Klippon® Automated RailLaser

Marking terminal blocks usually is a time-consuming process with a high risk of error. SNAP IN S-Series terminal block design has therefore been optimised for fully automated laser marking, which saves time – up to 90 % the Klippon® Automated RailLaser, in conjunction with the Weidmüller Configurator (WMC), achieves maximum marking quality and error-proofing.



- Klippon® Automated RailLaser**
- Up to 90 % time saving in marking process
 - Avoidance of incorrect markings due to the consistent use of data from eCAD programs when using the Weidmüller Configurator (WMC)
 - Excellent marking quality and highquality print image on a wide variety of materials


Ordering data	
Type	Order No.
RAILLASER	2705010000



Take a closer look at the Klippon® Automated RailLaser.
Just scan the QR code and watch the video.


Automated wiring

Full order books and a growing lack of skilled workers are driving digitalisation and automation in control cabinet production. That is why Klippon® Connect SNAP IN terminal blocks are already prepared for tomorrow's automation processes. The simple and safe handling of SNAP IN technology facilitates the use of automated wiring processes and prevents incorrect wiring.



S2C 1.51.5 mm²

SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-sectionA/mm²
Max. clamping rangemm²

3.5 x 54.5 x 33.5
17.5 / 1.5
0.34...1.5



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
500			
17.5			
1.5			
	6 kV / 3		
	A1 / V-0		



Rated connection

0.34...1.5 / 0.34...1.5
0.34...1.5 / 0.34...1
8 / 0.4 x 2.0 mm

Note

Ordering data

Version	Type	Qty.	Order No.
dark beige Blue Orange	S2C 1.5	50	2986540000
	S2C 1.5 BL	50	2986550000
	S2C 1.5 OR	50	2986560000

Note

Accessories

Plug-in cross-connection	Type	Qty.	Order No.
2-pole 10-pole	ZQV 1.5N/2	17.5 A 60	1985410000
	ZQV 1.5N/10	17.5 A 20	1985580000

End plate	Type	Qty.	Order No.
dark beige blue	AEP 2C 1.5	50	1552600000
	AEP 2C 1.5 BL	50	1552610000

End bracket	Type	Qty.	Order No.
dark beige, screwable dark beige, direct mounting	AEB 35 SC/1	50	1991920000
	AEB 35 SCL/1 V0	20	2661280000

Test adapter	Type	Qty.	Order No.
1-pole stackable 3-pole 5-pole	ATPG 1.5-10 L	0.2 A 50	1991890000
	ATPG 1.5 MI-R	0.2 A 50	1991880000

Test plug	Type	Qty.	Order No.
	PS 2.0 MC	20	0310000000


Screwdriver	Type	Qty.	Order No.
Standard	SDS 0.4X2.0X60	1	2749260000

Marking tags	Type	Qty.	Order No.
	WS 8/3.5 MM WS	1000	2007140000
	DEK 5/3.5 MM WS	1000	2007100000
	DEK 5/3.5 PLUS MC NE WS	1600	2003750000

For detailed information on other accessories and application in the online catalogue

S3C 1.51.5 mm²

SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-sectionA/mm²
Max. clamping rangemm²

3.5 x 61.5 x 33.5
17.5 / 1.5
0.34...1.5



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
500			
17.5			
1.5			
	6 kV / 3		
	A1 / V-0		



Rated connection

0.34...1.5 / 0.34...1.5
0.34...1.5 / 0.34...1
8 / 0.4 x 2.0 mm

Note

Ordering data

Type	Qty.	Order No.
S3C 1.5	50	2986580000
S3C 1.5 BL	50	2986590000
S3C 1.5 OR	50	2986600000

Note

Accessories

Type	Qty.	Order No.
ZQV 1.5N/2	17.5 A 60	1985410000
ZQV 1.5N/10	17.5 A 20	1985580000

Type	Qty.	Order No.
AEP 3C 1.5	50	1552620000
AEP 3C 1.5 BL	50	1552630000

Type	Qty.	Order No.
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

Type	Qty.	Order No.
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000

Type	Qty.	Order No.
PS 2.0 MC	20	0310000000

Type	Qty.	Order No.
SDS 0.4X2.0X60	1	2749260000


Type	Qty.	Order No.
WS 8/3.5 MM WS	1000	2007140000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000

For detailed information on other accessories and application in the online catalogue

Spring connection with SNAP IN technology (S-Series)
Feed-through terminal blocks

S4C 1.51.5 mm²


SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-sectionA/mm²
Max. clamping rangemm²

3.5 x 67.5 x 33.5
17.5 / 1.5
0.34...1.5



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
500			
17.5			
1.5			
	6 kV / 3		
	A1 / V-0		



Rated connection

0.34...1.5 / 0.34...1.5
0.34...1.5 / 0.34...1
8 / 0.4 x 2.0 mm

Note

Ordering data

Type	Qty.	Order No.
S4C 1.5	50	2986620000
S4C 1.5 BL	50	2986630000
S4C 1.5 OR	50	2986640000

Note

Accessories

Type	Qty.	Order No.
ZQV 1.5N/2	17.5 A 60	1985410000
ZQV 1.5N/10	17.5 A 20	1985580000

Type	Qty.	Order No.
AEP 4C 1.5	50	1552640000
AEP 4C 1.5 BL	50	1552650000

Type	Qty.	Order No.
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

Type	Qty.	Order No.
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000

Type	Qty.	Order No.
PS 2.0 MC	20	0310000000

Type	Qty.	Order No.
SDS 0.4X2.0X60	1	2749260000

Type	Qty.	Order No.
WS 8/3.5 MM WS	1000	2007140000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000


For detailed information on other accessories and application in the online catalogue

12

13

S2C 4

4 mm²



Width/Height/Depth	mm
max. current / max. cond. cross-section	A/mm ²
Max. clamping range	mm ²

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data


Version	dark beige Blue Orange
Note	

Accessories

Plug-in cross-connection	2-pole 10-pole 2-pole 10-pole
Vertical jumpers	1-pole
End plate	dark beige blue
End bracket	dark beige, screwable dark beige, direct mounting
Test adapter	1-pole stackable 3-pole 5-pole
Test plug	
Screwdriver	Standard
Marking tags	

For detailed information on other accessories and application in the online catalogue

S3C 4

4 mm²

$6.1 \times 78 \times 41.5$
 $32/4$
 $0.75...4$

IEC 60947-1			 II 2 GD Ex ib IIC Gb
IEC	UL	CSA	EN 60079-7
1000	600		550
32	30		29
4	AWG 20...10		4
100kA			
8 kV / 3			
A4 / V-0			
     			TÜV22ATEX8925U
Rated connection			
0.75...6 / 0.75...6			
0.75...6 / 0.75...4			
12 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S3C 4	50	2874840000
S3C 4 BL	50	2874850000
S3C 4 OR	50	3023550000

Type	Qty.	Order No.
ZQV 4N/2	32 A 60	1527930000
ZQV 4N/10	32 A 20	1528090000

SEP 3C 4	20	2874800000
----------	----	------------

AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

ATPG 1.5-10 L	0.2 A	50	1991890000
ATPG 4 MI-R	0.2 A	50	1991860000


PS 2.0 MC	20	0310000000
-----------	----	------------

SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------

WS 10/6 M PLUS MC NE WS	600	2003780000
WS 8/6 MM WS	600	2007160000
DEK 5/6 MM WS	600	2007120000
DEK 5/6 PLUS MC NE WS	1000	1011320000

© 2006 The Authors
Journal compilation © 2006 Blackwell Publishing Ltd

S4C 4

4 mm²

6.1 x 94 x 41.5
32 / 4
0.75...4

IEC 60947-1			 II 2 GD Ex eb IIC Gb
IEC	UL	CSA	EN 60079-7
1000	600		550
32	30		29
4	AWG 20...10		4
100kA			
8 kV / 3			
A4 / V-0			
      			TÜV22ATEX8925U
Rated connection			
0.75...6 / 0.75...6			
0.75...6 / 0.75...4			
12 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S4C 4	50	2874860000
S4C 4 BL	50	2874870000
S4C 4 OR	50	3023560000

Type	Qty.	Order No.
ZQV 4N/2	32 A 60	1527930000
ZQV 4N/10	32 A 20	1528090000

SEP 4C 4	20	2874810000
----------	----	------------

AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000


ATPG 1.5-10 L	0.2 A	50	1991890000
ATPG 4 MI-R	0.2 A	50	1991860000


PS 2.0 MC	20	0310000000
-----------	----	------------

SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------

WS 10/6 M PLUS MC NE WS	600	2003780000
WS 8/6 MM WS	600	2007160000
DEK 5/6 MM WS	600	2007120000
DEK 5/6 PLUS MC NE WS	1000	1011320000

© 2006 The Authors
Journal compilation © 2006 Blackwell Publishing Ltd

S2C 6		6 mm ²
		
Width/Height/Depth	mm	
max. current / max. cond. cross-section	A/mm ²	
Max. clamping range	mm ²	
Technical data		
Rated data		
Rated voltage	V	
Rated current	A	
for wire cross-section	mm ²	
Rated impulse withstand voltage / Pollution severity		
Gauge to IEC 60947-1 / UL 94 flammability rating		
Approvals		
Clamped conductors		
Solid / Stranded	mm ²	
Flexible / Flexible with ferrule	mm ²	
Stripping length / Blade size	mm/-	
Note		

S2C 6		6 mm ²
		
8.1 x 66.5 x 45.5		
41 / 10		
1.0...6		
		
IEC 60947-1		
IEC	UL	CSA
1000		
41		
6		
	8 kV / 3	
	A5 / V-0	
		
Rated connection		
1.0...6 / 1.0...6		
1.0...6 / 1.0...6		
12 / 1.0 x 5.5 mm		

Ordering data

Version	
	dark beige
	Blue
	Orange
Note	


Accessories

Plug-in cross-connection	2-pole 3-pole 4-pole
End plate	dark beige blue
End bracket	dark beige, screwable dark beige, direct mounting
Test adapter	1-pole stackable
Test plug	
Screwdriver	Standard
Marking tags	

For detailed information on other accessories and application in the online catalogue

S3C 6

6 mm²



Q4
2025

8.1 x 84.5 x 45.5

41 / 10

1.0...6



IEC 60947-1	UL	CSA	EN 60079-7
1000			
41			
6			
	8 kV / 3		
	A5 / V-0		





Rated connection

1.0...6 / 1.0...6

1.0...6 / 1.0...6

12 / 1.0 x 5.5 mm

Type	Qty.	Order No.
S3C 6	50	2935570000
S3C 6 BL	50	2935580000
S3C 6 OR	50	2935590000

Type		Qty.	Order No.
ZQV 6N/2	41 A	60	1985740000
ZQV 6N/3	41 A	60	1985760000
ZQV 6N/4	41 A	60	1985780000
SEP 3C 6		20	2935670000
AEB 35 SC/1		50	1991920000
AEB 35 SCL/1 VO		20	2661280000
ATPG 1.5-10 L	0.2 A	50	1991890000
ATPG 6 MI-R	0.2 A	50	1991930000
PS 2.0 MC		20	0310000000
SDIL 1.0X5.5X125		1	2749160000
DEK-A 5/8 MM WS		500	2448860000
WS-A 8/8 MM WS		500	2448930000
DEK 5/8 PLUS MC NE WS		800	1046350000
WS 10/8 PLUS MC NE WS		420	1905950000

S4C 6

6 mm²

SNAP IN 

Q4 2025

8.1 x 102 x 45.5

41 / 10

1.0...6

IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
1000			
41			
6			
8 kV / 3			
A5 / V-0			

Rated connection

1.0...6 / 1.0...6

1.0...6 / 1.0...6

12 / 1.0 x 5.5 mm


Type	Qty.	Order No.
S4C 6	50	2935600000
S4C 6 BL	50	2935610000
S4C 6 OR	50	2935620000

Type		Qty.	Order No.
ZQV 6N/2	41 A	60	1985740000
ZQV 6N/3	41 A	60	1985760000
ZQV 6N/4	41 A	60	1985780000
SEP 4C 6		20	2935680000
AEB 35 SC/1		50	1991920000
AEB 35 SCL/1 V0		20	2661280000
ATPG 1.5-10 L	0.2 A	50	1991890000
ATPG 6 M-R	0.2 A	50	1991930000
PS 2.0 MC		20	0310000000
SDIL 1.0X5.5X125		1	2749160000
DEK-A 5/8 MM WS		500	2448860000
WS-A 8/8 MM WS		500	2448930000
DEK 5/8 PLUS MC NE WS		800	1046350000
WS 10/8 PLUS MC NE WS		420	1905950000

SL2C 6

6 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²


Max. clamping range

mm²

8.2 x 42.2 x 62.8

41 / 10

1.5...10



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600	600	
41	40	40	
6	AWG 14...8	AWG 14...8	
	10kA		
	8 kV / 3		
	A5 / V-0		



Rated connection

1.5...10 / 1.5...10

1.5...10 / 1.5...6

12 / 1.0 x 5.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Version	
dark beige	
Blue	

Note

Accessories

Plug-in cross-connection	
2-pole	
3-pole	
4-pole	

End plate

dark beige

End bracket

dark beige, screwable

dark beige, direct mounting

Test adapter

1-pole

stackable

Test plug

Screwdriver

Standard


Marking tags

For detailed information on other accessories and application in the online catalogue

SL3C 6

6 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²

Max. clamping range

mm²

8.2 x 57.6 x 76.7

41 / 10

1.5...10



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600	600	
41	40	40	
6	AWG 14...8	AWG 14...8	
	10kA		
	8 kV / 3		
	A5 / V-0		



Rated connection

1.5...10 / 1.5...10

1.5...10 / 1.5...6

12 / 1.0 x 5.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Type	Qty.	Order No.
SL3C 6	50	3037410000
SL3C 6 BL	50	3037420000

Note

Accessories

Type	Qty.	Order No.
ZQV 6SL/2	41 A 60	3077580000
ZQV 6SL/3	41 A 60	3077590000
ZQV 6SL/4	41 A 60	3077600000

SLEP 3C 6

50

3037600000

AEB 35 SC/1

50

1991920000

| AEB 35 SCL/1 VO | 20 | 2661280000 |

ATPG 1.5-10 L

0.2 A 50

1991890000

| ATPG 6 MI-R | 0.2 A 50 | 1991930000 |

PS 2.0 MC

20

0310000000

| SDIL 1.0X5.5X125 | 1 | 2749160000 |

DEK-A 5/8 MM WS

500

2448860000

WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000


For detailed information on other accessories and application in the online catalogue

Spring connection with SNAP IN technology (S-Series)
Feed-through terminal blocks

SL4C 6

6 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²

Max. clamping range

mm²

8.2 x 57.6 x 90.6

41 / 10

1.5...10



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600	600	
41	40	40	
6	AWG 14...8	AWG 14...8	
	10kA		
	8 kV / 3		
	A5 / V-0		



Rated connection

1.5...10 / 1.5...10

1.5...10 / 1.5...6

12 / 1.0 x 5.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Type	Qty.	Order No.
SL4C 6	50	3037440000
SL4C 6 BL	50	3037450000

Note

Accessories

Type	Qty.	Order No.
ZQV 6SL/2	41 A 60	3077580000
ZQV 6SL/3	41 A 60	3077590000
ZQV 6SL/4	41 A 60	3077600000

SLEP 4C 6

50

3037640000

AEB 35 SC/1

50

1991920000

| AEB 35 SCL/1 VO | 20 | 2661280000 |

ATPG 1.5-10 L

0.2 A 50

1991890000

| ATPG 6 MI-R | 0.2 A 50 | 1991930000 |

PS 2.0 MC

20

0310000000

| SDIL 1.0X5.5X125 | 1 | 2749160000 |

DEK-A 5/8 MM WS

500

2448860000

WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue


20

21

SL2C 10

10 mm²

SNAP IN



10.2 x 72 x 48.8

57 / 16

1.5...16



DIN EN 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600	600	
57	55	55	
10	AWG 12...6	AWG 12...6	
10kA			
8 kV / 3			
A6 / V-0			



Rated connection

1.5...16 / 1.5...16

2.5...16 / 2.5...10

18 / 1.0 x 5.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Version	Type	Qty.	Order No.
dark beige	SL2C 10	25	3037500000
	SL2C 10 BL	25	3037510000

Note

Accessories


Plug-in cross-connection	2-pole
End plate	dark beige
End bracket	dark beige, screwable dark beige, direct mounting
Test adapter	1-pole
Test plug	
Screwdriver	Standard
Marking tags	

For detailed information on other accessories and application in the online catalogue

SL3C 10

10 mm²

SNAP IN



10.2 x 68.5 x 89.1

57 / 16

1.5...16



DIN EN 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600	600	
57	55	55	
10	AWG 12...6	AWG 12...6	
10kA			
8 kV / 3			
A6 / V-0			



Rated connection

1.5...16 / 1.5...16

2.5...16 / 2.5...10

18 / 1.0 x 5.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Type	Qty.	Order No.
SL3C 10	25	3037530000
SL3C 10 BL	25	3037540000

Note

Accessories


Type	Qty.	Order No.	
ZQV 10N/2	57 A	25	2497250000
SLEP 3C 10	20	3037670000	
AEB 35 SC/1	50	1991920000	
AEB 35 SCL/1 V0	20	2661280000	
ATPG 10 MI-R	0.2 A	50	1991870000
PS 2.0 MC	20	0310000000	
SDIL 1.0X5.5X125	1	2749160000	
DEK 5/5 PLUS MC NE WS	1000	1854490000	
DEK 5/8 PLUS MC NE WS	800	1046350000	
WS 10/8 PLUS MC NE WS	420	1905950000	

For detailed information on other accessories and application in the online catalogue

SL2C 16

16 mm²

SNAP IN



12.2 x 49.8 x 77.2

76 / 25

2.5...25



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
1000	600	600	
76	75	75	
16	AWG 10...4	AWG 10...4	
10kA			
8 kV / 3			
A7 / V-0			



Rated connection

2.5...25 / 2.5...25

4...25 / 2.5...16

18 / 1.0 x 5.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Type	Qty.	Order No.
SL2C 16	20	3037560000
SL2C 16 BL	20	3037570000

Note


Accessories

Type	Qty.	Order No.	
ZQV 16N/2	76 A	25	2497290000
SLEP 2C 16	20	3037680000	
AEB 35 SC/1	50	1991920000	
AEB 35 SCL/1 V0	20	2661280000	
ATPG 1.5-10 L	0.2 A	50	1991890000
PS 2.0 MC	20	0310000000	
SDIL 1.0X5.5X125	1	2749160000	
DEK 5/5 PLUS MC NE WS	1000	1854490000	
DEK 5/8 PLUS MC NE WS	800	1046350000	
WS 10/8 PLUS MC NE WS	420	1905950000	

For detailed information on other accessories and application in the online catalogue

S2T 2.52.5 mm²

SNAP IN



Width/Height/Depth	mm
max. current / max. cond. cross-section	A/mm ²
Max. clamping range	mm ²

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-
Note	

Ordering data


Version		
	dark beige	
	Blue	
	Orange	
Note		

Accessories

Plug-in cross-connection		
	2-pole	
	10-pole	
	2-pole	
	10-pole	
Vertical jumpers		
	1-pole	
End plate		
	dark beige	
	blue	
End bracket		
	dark beige, screwable	
	dark beige, direct mounting	
Test adapter		
	1-pole	
	stackable	
	3-pole	
	5-pole	
Test plug		
Screwdriver		
	Standard	
Marking tags		
For detailed information on other accessories and application in the online catalogue		

S2T 2.5 VL2.5 mm²

SNAP IN



5.1 x 95 x 52	
22 / 2.5	
0.34...2.5	

IEC 60947-7-1

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
800	600		550
22	20		19
2.5	AWG 20...14		2.5
	100kA		
	8 kV / 3		
	A2 / V-0		

CE

UL

CSA

IEC

EN

TÜV

22

ATEX

89

25

U

Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

Type

Qty.

Order No.

S2T 2.5 VL

50

2902430000

S2T 2.5 VL BL

50

2902440000

S2T 2.5 VL OR

50

2902450000

Type

Qty.

Order No.

ZQV 2.5N/2

24 A

60

1527540000

ZQV 2.5N/10

24 A

20

1527690000

Type

Qty.

Order No.

SEP 2T 2.5

20

2913480000

SEP 2T 2.5 BL

20

2913490000

Type

Qty.

Order No.

AEB 35 SC/1

50

1991920000

AEB 35 SCL/1 VO

20

2661280000

Type

Qty.

Order No.

ATPG 1.5-10 L

0.2 A

50

1991890000

ATPG 2.5 MI-R

0.2 A

50

1991960000

ATPG 2.5/3

0.2 A

25

2041190000

ATPG 2.5/5

0.2 A

25

2041180000

Type

Qty.

Order No.

PS 2.0 MC

20

0310000000

Type

Qty.

Order No.

SDIL 0.6X3.5X100

1

2749140000

Type

Qty.

Order No.

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS

600

2003770000

SNAPMARK I

50

1805880000

Type

Qty.

Order No.

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS

600

2003770000


SNAPMARK I

50

1805880000

S2T 2.5 N-FT2.5 mm²

SNAP IN



5.1 x 95 x 52	
22 / 2.5	
0.34...2.5	

IEC 60947-7-1

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
800	600		550
22	20		19
2.5	AWG 20...14		2.5
	100kA		
	8 kV / 3		
	A2 / V-0		

CE

UL

CSA

IEC

EN

TÜV

22

ATEX

89

25

U

Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

Type

Qty.

Order No.

S2T 2.5 N-FT

50

2902420000

Type

Qty.

Order No.

ZQV 2.5N/2

24 A

60

1527540000

ZQV 2.5N/10

24 A

20

1527690000

Type

Qty.

Order No.

SEP 2T 2.5

20

2913480000

SEP 2T 2.5 BL

20

2913490000

Type

Qty.

Order No.

AEB 35 SC/1

50

1991920000

AEB 35 SCL/1 VO

20

2661280000

Type

Qty.

Order No.

ATPG 1.5-10 L

0.2 A

50

1991890000

ATPG 2.5 MI-R

0.2 A

50

1991960000

ATPG 2.5/3

0.2 A

25

2041190000

ATPG 2.5/5

0.2 A

25

2041180000

Type

Qty.

Order No.

PS 2.0 MC

20

0310000000

Type

Qty.

Order No.

SDIL 0.6X3.5X100

1

2749140000

Type

Qty.

Order No.

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS

600

2003770000

SNAPMARK I

50

1805880000

Type

Qty.

Order No.

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS

600

2003770000


SNAPMARK I

50

1805880000

S2T 2.5 FT-PE2.5 mm²

SNAP IN



5.1 x 95 x 52	
24 / 2.5	
0.34...2.5	

IEC 60947-7-1. IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
800	600		550
24	20		19
2.5	AWG 20...14		2.5
	100kA		
	8 kV / 3		
	A2 / V-0		

CE

UL

CSA

IEC

EN

TÜV

22

ATEX

89

25

U

Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

Type

Qty.

Order No.

S2T 2.5 FT-PE

50

2902410000

Type

Qty.

Order No.

ZQV 2.5N/2

24 A

60

1527540000

ZQV 2.5N/10

24 A

20

1527690000

Type

Qty.

Order No.

SEP 2T 2.5

20

2913480000

SEP 2T 2.5 BL

20

2913490000

Type

Qty.

Order No.

AEB 35 SC/1

50

1991920000

AEB 35 SCL/1 VO

20

2661280000

Type

Qty.

Order No.

ATPG 1.5-10 L

0.2 A

50

1991890000

ATPG 2.5 MI-R

0.2 A

50

1991960000

ATPG 2.5/3

0.2 A

25

2041190000

ATPG 2.5/5

0.2 A

25

2041180000

Type

Qty.

Order No.

PS 2.0 MC

20

0310000000

Type

Qty.

Order No.

SDIL 0.6X3.5X100

1

2749140000

Type

Qty.

Order No.

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS

600

2003770000

SNAPMARK I

50

1805880000

Type

Qty.

Order No.

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS

600

2003770000

SNAPMARK I


50

1805880000

S2T 2.5 6C

2.5 mm²


SNAP IN



5.1 x 102.5 x 64.5

22 / 4

0.34...4



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
22			
2.5			
		8 kV / 3	
		A3 / V-0	

Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Version	
	dark beige
	Blue

Note

Accessories

Plug-in cross-connection	
	2-pole
	10-pole
	1-pole
	10-pole
	2-pole
	10-pole

End plate

dark beige

End bracket

dark beige, screwable

dark beige, direct mounting

Test adapter

1-pole

stackable

3-pole

5-pole

Test plug

Screwdriver

Standard


Marking tags

For detailed information on other accessories and application in the online catalogue

S2T 2.5 6C VL

2.5 mm²


SNAP IN



5.1 x 102.5 x 64.5

22 / 4

0.34...4



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
22			
2.5			
		8 kV / 3	
		A3 / V-0	

Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Type	Qty.	Order No.
S2T 2.5 6C	50	3093170000
S2T 2.5 6C BL	50	3093200000

Accessories

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
ZVQ 2.5/1.5	24 A 50	1720700000

SEP 2T 2.5 6C

20

3093280000

AEB 35 SC/1

50

1991920000

AEB 35 SCL/1 V0

20

2661280000

ATPG 1.5-10 L

0.2 A 50

1991890000

ATPG 2.5 MI-R

0.2 A 50

1991960000

ATPG 2.5/3

0.2 A 25

2041190000

ATPG 2.5/5

0.2 A 25

2041180000

PS 2.0 MC

20

0310000000

SDIL 0.6X3.5X100

1

2749140000

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000

WS 10/5 M PLUS MC NE WS


600

2003770000

S2T 2.5 6C FT-PE

2.5 mm²

SNAP IN



5.1 x 102.5 x 64.5

22 / 4

0.34...4



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
22			
2.5			
		8 kV / 3	
		A3 / V-0	

Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Technical data

Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Type	Qty.	Order No.
S2T 2.5 6C FT-PE	50	3093240000

Accessories

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000

SEP 2T 2.5 6C

20

3093280000

AEB 35 SC/1

50

1991920000

AEB 35 SCL/1 V0

20

2661280000

ATPG 1.5-10 L

0.2 A 50

1991890000

ATPG 2.5 MI-R

0.2 A 50

1991960000

ATPG 2.5/3

0.2 A 25

2041190000

ATPG 2.5/5

0.2 A 25

2041180000

PS 2.0 MC

20

0310000000

SDIL 0.6X3.5X100

1

2749140000

DEK 5/5 PLUS MC NE WS

1000

1854490000

DEK 5/5 MM WS

800

2007110000

WS 8/5 MM WS

800

2007150000



WS 10/5 M PLUS MC NE WS

600

2003770000


26

27


S2T 2.5 8C		2.5 mm ²
 		
Width/Height/Depth mm max. current / max. cond. cross-section A/mm ² Max. clamping range mm ²		5.1 x 127.5 x 64.5 22 / 4 0.34...4
		
Technical data		
Rated data		
Rated voltage	V	800
Rated current	A	22
for wire cross-section	mm ²	2.5
Rated impulse withstand voltage / Pollution severity		
Gauge to IEC 60947-1 / UL 94 flammability rating		
Approvals		
Clamped conductors		
Solid / Stranded	mm ²	0.5...2.5 / 0.5...4
Flexible / Flexible with ferrule	mm ²	0.5...4 / 0.5...2.5
Stripping length / Blade size	mm/-	10 / 0.6 x 3.5 mm
Note		
Ordering data		
Version		
	dark beige	
	Blue	
Note		
Accessories		
Plug-in cross-connection		
	2-pole	
	10-pole	
	1-pole	
	10-pole	
	2-pole	
	10-pole	
End plate		
	dark beige	
End bracket		
	dark beige, screwable	
	dark beige, direct mounting	
Test adapter		
	1-pole	
	stackable	
	3-pole	
	5-pole	
Test plug		
Screwdriver		
	Standard	
Marking tags		
For detailed information on other accessories and application in the online catalogue		
IEC 60947-7-1		
IEC	UL	CSA
800		
22		
2.5		
	8 kV / 3	
	A3 / V-0	
  		
Rated connection		
0.5...2.5 / 0.5...4		
0.5...4 / 0.5...2.5		
10 / 0.6 x 3.5 mm		
Type		
Qty.		
Order No.		
S2T 2.5 8C	50	3093100000
S2T 2.5 8C BL	50	3093110000
Type		
Qty.		
Order No.		
ZQV 2.5N/2	24 A	60
ZQV 2.5N/10	24 A	20
ZVQ 2.5/1.5	24 A	50
SEP 2T 2.5 8C		
	20	3093260000
AEB 35 SC/1		
	50	1991920000
AEB 35 SCL/1 V0		
	20	2661280000
ATPG 1.5-10 L		
	0.2 A	50
ATPG 2.5 MI-R		
	0.2 A	50
ATPG 2.5/3		
	0.2 A	25
ATPG 2.5/5		
	0.2 A	25
PS 2.0 MC		
	20	0310000000
SDIL 0.6X3.5X100		
	1	2749140000
DEK 5/5 PLUS MC NE WS		
	1000	1854490000
DEK 5/5 MM WS		
	800	2007110000
WS 8/5 MM WS		
	800	2007150000
WS 10/5 M PLUS MC NE WS		
	600	2003770000

S2T 2.5 8C VL2.5 mm²

SNAP IN E



5.1 x 127.5 x 64.5
22 / 4
0.34...4



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
22			
2.5			
	8 kV / 3		
	A3 / V-D		

CEULUS

Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Type	Qty.	Order No.
S2T 2.5 8C VL	50	3093120000
S2T 2.5 8C VL BL	50	3093130000


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000

SEP 2T 2.5 8C	20	3093260000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 MI-R	0.2 A 50	1991960000
ATPG 2.5/3	0.2 A 25	2041190000
ATPG 2.5/5	0.2 A 25	2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000


S2T 2.5 8C FT-PE

2.5 mm²

SNAPIN



5.1 x 127.5 x 64.5
22 / 4
0.34...4



IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
22			
2.5			
	8 kV / 3		
	A3 / V-0		

CE



US

Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm


Type	Qty.	Order No.
S2T 2.5 8C FT-PE	50	3093150000

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP 2T 2.5 8C	20	3093260000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 MI-R	0.2 A 50	1991960000
ATPG 2.5/3	0.2 A 25	2041190000
ATPG 2.5/5	0.2 A 25	2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000

S3T 2.5

2.5 mm²


SNAP IN



5.1 x 119 x 89

22 / 2.5

0.34...2.5



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²

Max. clamping range

mm²

Technical data	
Rated data	
Rated voltage	V
Rated current	A
for wire cross-section	mm ²
Short Circuit Current Rating (SCCR)	
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-
Note	

Ordering data	
Version	
	dark beige
	Blue
	Orange
Note	


Accessories	
Plug-in cross-connection	
	2-pole
	10-pole
	2-pole
	10-pole
Vertical jumpers	
	1-pole
End plate	
	dark beige
	blue
End bracket	
	dark beige, screwable
	dark beige, direct mounting
Test adapter	
	1-pole
	stackable
	3-pole
	5-pole
Test plug	
Screwdriver	
	Standard
Marking tags	

For detailed information on other accessories and application in the online catalogue

S3T 2.5 VL

2.5 mm²


SNAP IN



5.1 x 119 x 89

24 / 2.5

0.34...2.5



IEC 60947-7-1

IEC

UL

CSA

EN 60079-7

800

22

2.5

10kA

8 kV / 3

A3 / V-0



Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

IEC	UL	CSA	EN 60079-7
800			
22			
2.5			
	10kA		
	8 kV / 3		
	A3 / V-0		
			
Rated connection			
0.5...2.5 / 0.5...2.5			
0.5...2.5 / 0.5...2.5			
10 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S3T 2.5	50	2902530000
S3T 2.5 BL	50	2902540000


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
ZVQ 2.5/1.5	24 A 50	1720700000
SEP 3T 2.5		2902630000
SEP 3T 2.5 BL		2902640000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 MHR	0.2 A 50	1991960000
ATPG 2.5/3	0.2 A 25	2041190000
ATPG 2.5/5	0.2 A 25	2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

For detailed information on other accessories and application in the online catalogue

S3T 2.5 FT-FT-PE

2.5 mm²


SNAP IN



5.1 x 119 x 89

24 / 2.5

0.34...2.5



IEC 60947-7-1 (-7-2)

IEC

UL

CSA

EN 60079-7

800

24

2.5

10kA

6 kV / 3

A3 / V-0



Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

IEC	UL	CSA	EN 60079-7
800			
24			
2.5			
	10kA		
	8 kV / 3		
	A3 / V-0		
			
Rated connection			
0.5...2.5 / 0.5...2.5			
0.5...2.5 / 0.5...2.5			
10 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S3T 2.5 VL	50	2902570000
S3T 2.5 VL BL	50	2902580000


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
ZVQ 2.5/1.5	24 A 50	1720700000
SEP 3T 2.5		2902630000
SEP 3T 2.5 BL		2902640000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 MHR	0.2 A 50	1991960000
ATPG 2.5/3	0.2 A 25	2041190000
ATPG 2.5/5	0.2 A 25	2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

For detailed information on other accessories and application in the online catalogue

S3T 2.5 N-FT-PE

2.5 mm²


SNAP IN



5.1 x 119 x 89

24 / 2.5

0.34...2.5



IEC 60947-7-1 (-7-2)

IEC

UL

CSA

EN 60079-7

800

24

2.5

10kA

8 kV / 3

A3 / V-0



Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

IEC	UL	CSA	EN 60079-7
800			
24			
2.5			
	10kA		
	6 kV / 3		
	A3 / V-0		
			
Rated connection			
0.5...2.5 / 0.5...2.5			
0.5...2.5 / 0.5...2.5			
10 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S3T 2.5 FT-FT-PE	50	2902550000


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
ZVQ 2.5/1.5	24 A 50	1720700000
SEP 3T 2.5		2902630000
SEP 3T 2.5 BL		2902640000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 MHR	0.2 A 50	1991960000
ATPG 2.5/3	0.2 A 25	2041190000
ATPG 2.5/5	0.2 A 25	2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

For detailed information on other accessories and application in the online catalogue

S3T 2.5 N-FT-PE

2.5 mm²


SNAP IN



5.1 x 119 x 89

24 / 2.5

0.34...2.5



IEC 60947-7-1 (-7-2)

IEC

UL

CSA

EN 60079-7

800

24

2.5

10kA

8 kV / 3

A3 / V-0



Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.5...2.5

10 / 0.6 x 3.5 mm

IEC	UL	CSA	EN 60079-7
800			
24			
2.5			
	10kA		
	8 kV / 3		
	A3 / V-0		
			
Rated connection			
0.5...2.5 / 0.5...2.5			
0.5...2.5 / 0.5...2.5			
10 / 0.6 x 3.5 mm			


Type	Qty.	Order No.
S3T 2.5 N-FT-PE	50	2902560000

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
ZVQ 2.5/1.5	24 A 50	1720700000
SEP 3T 2.5		2902630000
SEP 3T 2.5 BL		2902640000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 MHR	0.2 A 50	1991960000
ATPG 2.5/3	0.2 A 25	2041190000
ATPG 2.5/5	0.2 A 25	2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

For detailed information on other accessories and application in the online catalogue

S2C 1.5 PE1.5 mm²

SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

Technical data

Rated data	
for wire cross-section	mm²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm²
Flexible / Flexible with ferrule	mm²
Stripping length / Blade size	mm/-
Note	


Ordering data

Version	Green/yellow
Note	

Accessories

End plate	dark beige blue
End bracket	dark beige, screwable dark beige, direct mounting
Test adapter	1-pole stackable 3-pole 5-pole
Test plug	
Screwdriver	
Marking tags	Standard

For detailed information on other accessories and application in the online catalogue

3.5 x 54.5 x 33.5 / 1.5 0.34...1.5	
--	---


IEC 60947-7-2	IEC	UL	CSA	EN 60079-7
1.5				
500				
6				
180 A (1.5 mm²)				
3				
A1 / V-0				
CE cULus				
Rated connection				
0.34...1.5 / 0.34...1.5				
0.34...1.5 / 0.34...1				
8 / 0.4 x 2.0 mm				

Type	Qty.	Order No.
S2C 1.5 PE	50	2986570000

Type	Qty.	Order No.
AEP 2C 1.5	50	1552600000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000
PS 2.0 MC	20	0310000000
SDS 0.4X2.0X60	1	2749260000
WS 10/3.5 PLUS MC NE WS	960	2003760000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000

S3C 1.5 PE1.5 mm²

SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

Technical data

Rated data	
for wire cross-section	mm²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm²
Flexible / Flexible with ferrule	mm²
Stripping length / Blade size	mm/-
Note	


Ordering data

Type	Qty.	Order No.
S3C 1.5 PE	50	2986610000

Accessories

Type	Qty.	Order No.
AEP 3C 1.5	50	1552620000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000
PS 2.0 MC	20	0310000000
SDS 0.4X2.0X60	1	2749260000
WS 10/3.5 PLUS MC NE WS	960	2003760000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000

For detailed information on other accessories and application in the online catalogue

3.5 x 61.5 x 33.5 / 1.5 0.34...1.5	
--	---


IEC 60947-7-2	IEC	UL	CSA	EN 60079-7
1.5				
500				
6				
180 A (1.5 mm²)				
3				
A1 / V-0				
CE cULus				
Rated connection				
0.34...1.5 / 0.34...1.5				
0.34...1.5 / 0.34...1				
8 / 0.4 x 2.0 mm				

Type	Qty.	Order No.
S3C 1.5 PE	50	2986610000

Type	Qty.	Order No.
AEP 3C 1.5	50	1552620000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000
PS 2.0 MC	20	0310000000
SDS 0.4X2.0X60	1	2749260000
WS 10/3.5 PLUS MC NE WS	960	2003760000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000

S4C 1.5 PE1.5 mm²

SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

Technical data

Rated data	
for wire cross-section	mm²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm²
Flexible / Flexible with ferrule	mm²
Stripping length / Blade size	mm/-
Note	


Ordering data

Type	Qty.	Order No.
S4C 1.5 PE	50	2986650000

Accessories

Type	Qty.	Order No.
AEP 4C 1.5	50	1552640000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000
PS 2.0 MC	20	0310000000
SDS 0.4X2.0X60	1	2749260000
WS 10/3.5 PLUS MC NE WS	960	2003760000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000

For detailed information on other accessories and application in the online catalogue

3.5 x 67.5 x 33.5 / 1.5 0.34...1.5	
--	---

IEC 60947-7-2	IEC	UL	CSA	EN 60079-7
1.5				
500				
6				
180 A (1.5 mm²)				
3				
A1 / V-0				
CE cULus				
Rated connection				
0.34...1.5 / 0.34...1.5				
0.34...1.5 / 0.34...1				
8 / 0.4 x 2.0 mm				

Type	Qty.	Order No.
S4C 1.5 PE	50	2986650000

Type	Qty.	Order No.
AEP 4C 1.5	50	1552640000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 1.5 MI-R	0.2 A 50	1991880000
PS 2.0 MC	20	0310000000
SDS 0.4X2.0X60	1	2749260000
WS 10/3.5 PLUS MC NE WS	960	2003760000
DEK 5/3.5 MM WS	1000	2007100000
DEK 5/3.5 PLUS MC NE WS	1600	2003750000


32

33

S2C 2.5 PE


2.5 mm²

SNAP IN



Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

5.1 x 59 x 38
/ 2.5
0.34...2.5



IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
2.5	AWG 20...14	AWG 20...14	2.5
800			
8			
	100kA		
	300 A (2.5 mm ²)		
	3		
	A2 / V-0		

CE

UL

CSA

EN

TÜV

22

ATEX

8925U

Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.34...2.5

10 / 0.6 x 3.5 mm

Note

Version
Green/yellow
Note


Accessories
End plate
dark beige
blue
End bracket
dark beige, screwable
dark beige, direct mounting
Test adapter
1-pole
stackable
3-pole
5-pole
Test plug
Screwdriver
Standard
Marking tags

For detailed information on other accessories and application in the online catalogue

S3C 2.5 PE


2.5 mm²

SNAP IN



Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

5.1 x 71.5 x 38
/ 2.5
0.34...2.5



IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
2.5	AWG 20...14	AWG 20...14	2.5
800			
8			
	100kA		
	300 A (2.5 mm ²)		
	3		
	A2 / V-0		

CE

UL

CSA

EN

TÜV

22

ATEX

8925U

Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.34...2.5

10 / 0.6 x 3.5 mm

Note

Type	Qty.	Order No.
S3C 2.5 PE	50	2674570000


Type	Qty.	Order No.
SEP 3C 2.5	20	2751090000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A	50 1991890000
ATPG 2.5 MI-R	0.2 A	50 1991960000
ATPG 2.5/3	0.2 A	25 2041190000
ATPG 2.5/5	0.2 A	25 2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000

For detailed information on other accessories and application in the online catalogue

S4C 2.5 PE

2.5 mm²

SNAP IN



Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

5.1 x 84 x 38
/ 2.5
0.34...2.5



IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
2.5	AWG 20...14	AWG 20...14	2.5
800			
8			
	100kA		
	300 A (2.5 mm ²)		
	3		
	A2 / V-0		

CE

UL

CSA

EN

TÜV

22

ATEX

8925U

Rated connection

0.5...2.5 / 0.5...2.5

0.5...2.5 / 0.34...2.5

10 / 0.6 x 3.5 mm

Note

Type	Qty.	Order No.
S4C 2.5 PE	50	2674580000

Type	Qty.	Order No.
SEP 4C 2.5	20	2751100000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A	50 1991890000
ATPG 2.5 MI-R	0.2 A	50 1991960000
ATPG 2.5/3	0.2 A	25 2041190000
ATPG 2.5/5	0.2 A	25 2041180000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000

For detailed information on other accessories and application in the online catalogue

S2C 4 PE

4 mm²

SNAP IN

Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

Technical data

Rated data	
for wire cross-section	mm ²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Short Circuit Current Rating (SCCR)	
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-
Note	

Version
Green/yellow
Note

Accessories
End plate dark beige blue
End bracket dark beige, screwable dark beige, direct mounting
Test adapter 1-pole stackable 3-pole 5-pole
Test plug
Screwdriver Standard
Marking tags

For detailed information on other accessories and application in the online catalogue

S3C 4 PE

4 mm²

SNAP IN

6.1 x 62 x 41.5
/ 4
0.75...4

IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
4	AWG 20...10	AWG 20...10	4
1000			
8			
	100kA		
	480 A (4 mm ²)		
	3		
	A4 / V-0		
CE cRUUSExccSDIL			
TÜV22ATEX8925U			
Rated connection			
0.75...6 / 0.75...6			
0.75...6 / 0.75...4			
12 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S2C 4 PE	50	2874880000

Type	Qty.	Order No.
SEP 2C 4	20	2874790000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 4 M/R	0.2 A 50	1991860000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
WS 10/6 M PLUS MC NE WS	600	2003780000
WS 8/6 MM WS	600	2007160000
DEK 5/6 MM WS	600	2007120000
DEK 5/6 PLUS MC NE WS	1000	1011320000

S4C 4 PE

4 mm²

SNAP IN

6.1 x 78 x 41.5
/ 4
0.75...4

IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
4	AWG 20...10	AWG 20...10	4
1000			
8			
	100kA		
	480 A (4 mm ²)		
	3		
	A4 / V-0		
CE cRUUSExccSDIL			
TÜV22ATEX8925U			
Rated connection			
0.75...6 / 0.75...6			
0.75...6 / 0.75...4			
12 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S3C 4 PE	50	2874890000

Type	Qty.	Order No.
SEP 3C 4	20	2874800000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 2.5 M/R	0.2 A 50	1991960000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000

For detailed information on other accessories and application in the online catalogue

S4C 4 PE

4 mm²

SNAP IN

6.1 x 94 x 41.5
/ 4
0.75...4

IEC 60947-7-2

Ex II 2 GD
Ex eb IIC Gb

IEC	UL	CSA	EN 60079-7
4	AWG 20...10	AWG 20...10	4
1000			
8			
	100kA		
	480 A (4 mm ²)		
	3		
	A4 / V-0		
CE cRUUSExccSDIL			
TÜV22ATEX8925U			
Rated connection			
0.75...6 / 0.75...6			
0.75...6 / 0.75...4			
12 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
S4C 4 PE	50	2874900000

Type	Qty.	Order No.
SEP 4C 4	20	2874810000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
ATPG 4 M/R	0.2 A 50	1991860000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
WS 10/6 M PLUS MC NE WS	600	2003780000
WS 8/6 MM WS	600	2007160000
DEK 5/6 MM WS	600	2007120000
DEK 5/6 PLUS MC NE WS	1000	1011320000


For detailed information on other accessories and application in the online catalogue

36

37


S2C 6 PE6 mm²

SNAP IN



Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

8.1 x 66.5 x 45.5
/ 10
0.34...10



Technical data

Rated data	
for wire cross-section	mm ²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Ordering data

Version	Green/yellow
---------	--------------

Note


Accessories

End plate	dark beige blue
End bracket	dark beige, screwable dark beige, direct mounting
Test adapter	1-pole stackable 3-pole 5-pole
Test plug	
Screwdriver	
Marking tags	Standard

For detailed information on other accessories and application in the online catalogue

S3C 6 PE6 mm²


SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

8.1 x 84.5 x 45.5
/ 10
0.34...10



Technical data

IEC 60947-7-2	
IEC	UL
6	
1000	
8	
	720 A (6 mm ²)
	3
	A5 / V-0
CECSULUS	
Rated connection	
0.5...6 / 0.5...6	
0.5...10 / 0.5...6	
12 / 1.0 x 5.5 mm	

Note

Ordering data

Type	Qty.	Order No.
S2C 6 PE	50	2935630000

Note

Accessories

Type	Qty.	Order No.
SEP 2C 6	20	2935660000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A	501991890000
ATPG 6 MI-R	0.2 A	501991930000
PS 2.0 MC	20	0310000000
SDIL 1.0X5.5X125	1	2749160000
DEK-A 5/8 MM WS	500	2448860000
WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue

S4C 6 PE6 mm²


SNAP IN



Q4 2025

Width/Height/Depthmm
max. current / max. cond. cross-section-/mm²
Max. clamping rangemm²

8.1 x 102 x 45.5
41 / 10
0.34...10



Technical data

IEC 60947-7-2	
IEC	UL
6	
1000	
8	
	720 A (6 mm ²)
	3
	A5 / V-0
CECSULUS	
Rated connection	
0.5...6 / 0.5...6	
0.5...10 / 0.5...6	
12 / 1.0 x 5.5 mm	

Note

Ordering data

Type	Qty.	Order No.
S4C 6 PE	50	2935650000

Note

Accessories

Type	Qty.	Order No.
SEP 4C 6	20	2935680000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A	501991890000
ATPG 6 MI-R	0.2 A	501991930000
PS 2.0 MC	20	0310000000
SDIL 1.0X5.5X125	1	2749160000
DEK-A 5/8 MM WS	500	2448860000
WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue


38

39

SL2C 6 PE

6 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

-/mm²


Max. clamping range

mm²

10.2 x 72 x 48.8

/ 16

1.5...16



IEC 60947-7-2

IEC	UL	CSA	EN 60079-7
6	AWG 14...8	AWG 14...8	
1000			
8			
	10kA		
	720 A (6 mm ²)		
	3		
	A5 / V-0		

CE

CE

c

RU

US

UL

Rated connection

1.5...10 / 1.5...10

1.5...10 / 1.5...6

12 / 1.0 x 5.5 mm

Note

Ordering data

Version	Qty.	Order No.
Green/yellow	50	3037400000

Note

Accessories

End plate	Qty.	Order No.
dark beige	50	3037590000

End bracket	Qty.	Order No.
dark beige, screwable	50	1991920000
dark beige, direct mounting	20	2661280000

Test adapter	Qty.	Order No.
1-pole	50	1991890000
stackable	50	1991930000
3-pole		
5-pole		

Test plug	Qty.	Order No.
PS 2.0 MC	20	0310000000

Screwdriver	Qty.	Order No.
SDIL 1.0X5.5X125	1	2749160000

Marking tags	Qty.	Order No.
DEK-A 5/8 MM WS	500	2448860000
WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue

SL3C 6 PE

6 mm²


SNAP IN



8.2 x 57.6 x 76.7

/ 10

1.5...10



IEC 60947-7-2

IEC	UL	CSA	EN 60079-7
6	AWG 14...8	AWG 14...8	
1000			
8			
	10kA		
	720 A (6 mm ²)		
	3		
	A5 / V-0		

CE

CE

c

RU

US

UL

Rated connection

1.5...10 / 1.5...10

1.5...10 / 1.5...6

12 / 1.0 x 5.5 mm

Note

Ordering data

Type	Qty.	Order No.
SL3C 6 PE	50	3037430000

Note

Accessories

Type	Qty.	Order No.
SLEP 3C 6	50	3037600000

Type	Qty.	Order No.
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

Type	Qty.	Order No.
ATPG 1.5-10 L	50	1991890000
ATPG 6 MI-R	50	1991930000

Type	Qty.	Order No.
PS 2.0 MC	20	0310000000

Type	Qty.	Order No.
SDIL 1.0X5.5X125	1	2749160000


Type	Qty.	Order No.
DEK-A 5/8 MM WS	500	2448860000
WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue

SL4C 6 PE

6 mm²


SNAP IN



8.2 x 57.6 x 90.6

/ 10

1.5...10



IEC 60947-7-2

IEC	UL	CSA	EN 60079-7
6	AWG 14...8	AWG 14...8	
1000			
8			
	10kA		
	720 A (6 mm ²)		
	3		
	A5 / V-0		

CE

CE

c

RU

US

UL

Rated connection

1.5...10 / 1.5...10

1.5...10 / 1.5...6

12 / 1.0 x 5.5 mm

Note

Ordering data

Type	Qty.	Order No.
SL4C 6 PE	50	3037460000

Note

Accessories

Type	Qty.	Order No.
SLEP 4C 6	50	3037640000

Type	Qty.	Order No.
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

Type	Qty.	Order No.
ATPG 1.5-10 L	50	1991890000
ATPG 6 MI-R	50	1991930000

Type	Qty.	Order No.
PS 2.0 MC	20	0310000000

Type	Qty.	Order No.
SDIL 1.0X5.5X125	1	2749160000

Type	Qty.	Order No.
DEK-A 5/8 MM WS	500	2448860000
WS-A 8/8 MM WS	500	2448930000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue

40

41

SL2C 10 PE10 mm²

SNAP IN



Width/Height/Depth	mm
max. current / max. cond. cross-section	-/mm²
Max. clamping range	mm²

10.2 x 72 x 48.8
/ 16
1.5...16

Technical data

Rated data	
for wire cross-section	mm²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Short Circuit Current Rating (SCCR)	
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm²
Flexible / Flexible with ferrule	mm²
Stripping length / Blade size	mm/-
Note	

Ordering data

Version
Green/yellow
Note

Accessories

End plate	dark beige
End bracket	dark beige, screwable dark beige, direct mounting
Test adapter	1-pole stackable 3-pole 5-pole
Test plug	
Screwdriver	Standard
Marking tags	

For detailed information on other accessories and application in the online catalogue

SL3C 10 PE10 mm²

SNAP IN



10.2 x 68.5 x 89.1
/ 16
1.5...16

Technical data

Rated data	
for wire cross-section	mm²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Short Circuit Current Rating (SCCR)	
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm²
Flexible / Flexible with ferrule	mm²
Stripping length / Blade size	mm/-
Note	


Type	Qty.	Order No.
SL3C 10 PE	25	3037550000

Type	Qty.	Order No.
SLEP 3C 10	50	3037670000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
PS 2.0 MC	20	0310000000
SDIL 1.0X5.5X125	1	2749160000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000

For detailed information on other accessories and application in the online catalogue

SL2C 16 PE16 mm²

SNAP IN



12.2 x 49.8 x 77.2
/ 25
2.5...25


Technical data

Rated data	
for wire cross-section	mm²
Rated voltage to adjoining terminal	V
Rated impulse withstand voltage to adjacent terminal	kV
Short Circuit Current Rating (SCCR)	
Rated short-time current	
Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Approvals	
Clamped conductors	
Solid / Stranded	mm²
Flexible / Flexible with ferrule	mm²
Stripping length / Blade size	mm/-
Note	

Type	Qty.	Order No.
SL2C 16 PE	50	3037580000

Type	Qty.	Order No.
SLEP 2C 16	50	3037680000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
ATPG 1.5-10 L	0.2 A 50	1991890000
PS 2.0 MC	20	0310000000
SDIL 1.0X5.5X125	1	2749160000
DEK 5/5 PLUS MC NE WS	1000	1854490000
WS-A 8/12 MM WS	300	2619900000
DEK 5/8 PLUS MC NE WS	800	1046350000
WS 10/8 PLUS MC NE WS	420	1905950000


For detailed information on other accessories and application in the online catalogue

S2T 2.5 PE	2.5 mm ²																												
SNAP IN 																													
Width/Height/Depth	mm																												
max. current / max. cond. cross-section	-/mm ²																												
Max. clamping range	mm ²																												
Technical data <table><tr><td>Rated data</td><td></td></tr><tr><td>for wire cross-section</td><td>mm²</td></tr><tr><td>Rated voltage to adjoining terminal</td><td>V</td></tr><tr><td>Rated impulse withstand voltage to adjacent terminal</td><td>kV</td></tr><tr><td>Short Circuit Current Rating (SCCR)</td><td></td></tr><tr><td>Rated short-time current</td><td></td></tr><tr><td>Pollution severity</td><td></td></tr><tr><td>Gauge to IEC 60947-1 / UL 94 flammability rating</td><td></td></tr><tr><td>Approvals</td><td></td></tr><tr><td>Clamped conductors</td><td></td></tr><tr><td>Solid / Stranded</td><td>mm²</td></tr><tr><td>Flexible / Flexible with ferrule</td><td>mm²</td></tr><tr><td>Stripping length / Blade size</td><td>mm/-</td></tr><tr><td>Note</td><td></td></tr></table> 5.1 x 95 x 52 / 2.5 0.34...2.5  IEC 60947-7-2 UL CSA EN 60079-7 2.5 800 6 100kA 300 A (2.5 mm²) 3 A2 / V-0  TÜV22ATEX8925U Rated connection 0.5...2.5 / 0.5...2.5 0.5...2.5 / 0.5...2.5 10 / 0.6 x 3.5 mm		Rated data		for wire cross-section	mm ²	Rated voltage to adjoining terminal	V	Rated impulse withstand voltage to adjacent terminal	kV	Short Circuit Current Rating (SCCR)		Rated short-time current		Pollution severity		Gauge to IEC 60947-1 / UL 94 flammability rating		Approvals		Clamped conductors		Solid / Stranded	mm ²	Flexible / Flexible with ferrule	mm ²	Stripping length / Blade size	mm/-	Note	
Rated data																													
for wire cross-section	mm ²																												
Rated voltage to adjoining terminal	V																												
Rated impulse withstand voltage to adjacent terminal	kV																												
Short Circuit Current Rating (SCCR)																													
Rated short-time current																													
Pollution severity																													
Gauge to IEC 60947-1 / UL 94 flammability rating																													
Approvals																													
Clamped conductors																													
Solid / Stranded	mm ²																												
Flexible / Flexible with ferrule	mm ²																												
Stripping length / Blade size	mm/-																												
Note																													

Ordering data
Version
Green/yellow
Note

Accessories
End plate
dark beige
blue
End bracket
dark beige, screwable
dark beige, direct mounting
Test adapter
1-pole
stackable
3-pole
5-pole
Test plug
Screwdriver
Standard
Marking tags


For detailed information on other accessories and application in the online catalogue

S2T 2.5 6C PE	2.5 mm ²																												
SNAP IN 																													
Width/Height/Depth	mm																												
max. current / max. cond. cross-section	-/mm ²																												
Max. clamping range	mm ²																												
Technical data <table><tr><td>Rated data</td><td></td></tr><tr><td>for wire cross-section</td><td>mm²</td></tr><tr><td>Rated voltage to adjoining terminal</td><td>V</td></tr><tr><td>Rated impulse withstand voltage to adjacent terminal</td><td>kV</td></tr><tr><td>Short Circuit Current Rating (SCCR)</td><td></td></tr><tr><td>Rated short-time current</td><td></td></tr><tr><td>Pollution severity</td><td></td></tr><tr><td>Gauge to IEC 60947-1 / UL 94 flammability rating</td><td></td></tr><tr><td>Approvals</td><td></td></tr><tr><td>Clamped conductors</td><td></td></tr><tr><td>Solid / Stranded</td><td>mm²</td></tr><tr><td>Flexible / Flexible with ferrule</td><td>mm²</td></tr><tr><td>Stripping length / Blade size</td><td>mm/-</td></tr><tr><td>Note</td><td></td></tr></table> 5.1 x 102.5 x 64.5 / 2.5 0.34...2.5  IEC 60947-7-2 UL CSA EN 60079-7 2.5 800 8 100kA 300 A (2.5 mm²) 3 A3 / V-0  Rated connection 0.5...2.5 / 0.5...2.5 0.5...2.5 / 0.5...2.5 10 / 0.6 x 3.5 mm		Rated data		for wire cross-section	mm ²	Rated voltage to adjoining terminal	V	Rated impulse withstand voltage to adjacent terminal	kV	Short Circuit Current Rating (SCCR)		Rated short-time current		Pollution severity		Gauge to IEC 60947-1 / UL 94 flammability rating		Approvals		Clamped conductors		Solid / Stranded	mm ²	Flexible / Flexible with ferrule	mm ²	Stripping length / Blade size	mm/-	Note	
Rated data																													
for wire cross-section	mm ²																												
Rated voltage to adjoining terminal	V																												
Rated impulse withstand voltage to adjacent terminal	kV																												
Short Circuit Current Rating (SCCR)																													
Rated short-time current																													
Pollution severity																													
Gauge to IEC 60947-1 / UL 94 flammability rating																													
Approvals																													
Clamped conductors																													
Solid / Stranded	mm ²																												
Flexible / Flexible with ferrule	mm ²																												
Stripping length / Blade size	mm/-																												
Note																													

Type	Qty.	Order No.
S2T 2.5 6C PE	50	3093250000

Type	Qty.	Order No.
SEP 2C 6	50	1991970000
SEP 2C 6 BL	50	1991950000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A	50 1991890000
ATPG 2.5 MI-R	0.2 A	50 1991960000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000


For detailed information on other accessories and application in the online catalogue

S2T 2.5 8C PE	2.5 mm ²																												
SNAP IN 																													
Width/Height/Depth	mm																												
max. current / max. cond. cross-section	-/mm ²																												
Max. clamping range	mm ²																												
Technical data <table><tr><td>Rated data</td><td></td></tr><tr><td>for wire cross-section</td><td>mm²</td></tr><tr><td>Rated voltage to adjoining terminal</td><td>V</td></tr><tr><td>Rated impulse withstand voltage to adjacent terminal</td><td>kV</td></tr><tr><td>Short Circuit Current Rating (SCCR)</td><td></td></tr><tr><td>Rated short-time current</td><td></td></tr><tr><td>Pollution severity</td><td></td></tr><tr><td>Gauge to IEC 60947-1 / UL 94 flammability rating</td><td></td></tr><tr><td>Approvals</td><td></td></tr><tr><td>Clamped conductors</td><td></td></tr><tr><td>Solid / Stranded</td><td>mm²</td></tr><tr><td>Flexible / Flexible with ferrule</td><td>mm²</td></tr><tr><td>Stripping length / Blade size</td><td>mm/-</td></tr><tr><td>Note</td><td></td></tr></table> 5.1 x 127.5 x 64.5 / 2.5 0.34...2.5  IEC 60947-7-2 UL CSA EN 60079-7 2.5 800 8 100kA 300 A (2.5 mm²) 3 A3 / V-0  Rated connection 0.5...2.5 / 0.5...2.5 0.5...2.5 / 0.5...2.5 10 / 0.6 x 3.5 mm		Rated data		for wire cross-section	mm ²	Rated voltage to adjoining terminal	V	Rated impulse withstand voltage to adjacent terminal	kV	Short Circuit Current Rating (SCCR)		Rated short-time current		Pollution severity		Gauge to IEC 60947-1 / UL 94 flammability rating		Approvals		Clamped conductors		Solid / Stranded	mm ²	Flexible / Flexible with ferrule	mm ²	Stripping length / Blade size	mm/-	Note	
Rated data																													
for wire cross-section	mm ²																												
Rated voltage to adjoining terminal	V																												
Rated impulse withstand voltage to adjacent terminal	kV																												
Short Circuit Current Rating (SCCR)																													
Rated short-time current																													
Pollution severity																													
Gauge to IEC 60947-1 / UL 94 flammability rating																													
Approvals																													
Clamped conductors																													
Solid / Stranded	mm ²																												
Flexible / Flexible with ferrule	mm ²																												
Stripping length / Blade size	mm/-																												
Note																													

Type	Qty.	Order No.
S2T 2.5 8C PE	50	3093160000

Type	Qty.	Order No.
SEP 3C 6	50	1991940000
SEP 3C 6 BL	20	1991910000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A	50 1991890000
ATPG 2.5 MI-R	0.2 A	50 1991960000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

For detailed information on other accessories and application in the online catalogue

S3T 2.5 PE	2.5 mm ²																												
SNAP IN 																													
Width/Height/Depth	mm																												
max. current / max. cond. cross-section	-/mm ²																												
Max. clamping range	mm ²																												
Technical data <table><tr><td>Rated data</td><td></td></tr><tr><td>for wire cross-section</td><td>mm²</td></tr><tr><td>Rated voltage to adjoining terminal</td><td>V</td></tr><tr><td>Rated impulse withstand voltage to adjacent terminal</td><td>kV</td></tr><tr><td>Short Circuit Current Rating (SCCR)</td><td></td></tr><tr><td>Rated short-time current</td><td></td></tr><tr><td>Pollution severity</td><td></td></tr><tr><td>Gauge to IEC 60947-1 / UL 94 flammability rating</td><td></td></tr><tr><td>Approvals</td><td></td></tr><tr><td>Clamped conductors</td><td></td></tr><tr><td>Solid / Stranded</td><td>mm²</td></tr><tr><td>Flexible / Flexible with ferrule</td><td>mm²</td></tr><tr><td>Stripping length / Blade size</td><td>mm/-</td></tr><tr><td>Note</td><td></td></tr></table> 5.1 x 119 x 89 / 2.5 0.34...2.5  IEC 60947-7-2 UL CSA EN 60079-7 2.5 800 8 100kA 300 A (2.5 mm²) 3 A3 / V-0  Rated connection 0.5...2.5 / 0.5...2.5 0.5...2.5 / 0.5...2.5 10 / 0.6 x 3.5 mm		Rated data		for wire cross-section	mm ²	Rated voltage to adjoining terminal	V	Rated impulse withstand voltage to adjacent terminal	kV	Short Circuit Current Rating (SCCR)		Rated short-time current		Pollution severity		Gauge to IEC 60947-1 / UL 94 flammability rating		Approvals		Clamped conductors		Solid / Stranded	mm ²	Flexible / Flexible with ferrule	mm ²	Stripping length / Blade size	mm/-	Note	
Rated data																													
for wire cross-section	mm ²																												
Rated voltage to adjoining terminal	V																												
Rated impulse withstand voltage to adjacent terminal	kV																												
Short Circuit Current Rating (SCCR)																													
Rated short-time current																													
Pollution severity																													
Gauge to IEC 60947-1 / UL 94 flammability rating																													
Approvals																													
Clamped conductors																													
Solid / Stranded	mm ²																												
Flexible / Flexible with ferrule	mm ²																												
Stripping length / Blade size	mm/-																												
Note																													


Type	Qty.	Order No.
S3T 2.5 PE	50	2902590000

Type	Qty.	Order No.
SEP 4C 6	50	2876180000
SEP 4C 6 BL	50	2876190000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 VO	20	2661280000
ATPG 1.5-10 L	0.2 A	50 1991890000
ATPG 2.5 MI-R	0.2 A	50 1991960000
PS 2.0 MC	20	0310000000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

For detailed information on other accessories and application in the online catalogue

Spring connection with SNAP IN technology (S-Series)
Fuse terminals blocks

SFS 4 2C BK		4 mm ²
SNAP IN 		
Width/Height/Depth	mm	
max. current / max. cond. cross-section	A/mm ²	
Max. clamping range	mm ²	
Technical data		
Rated data		
Rated voltage to adjoining terminal	V	
Rated current	A	
for wire cross-section	mm ²	
Short Circuit Current Rating (SCCR)		
Rated impulse withstand voltage / Pollution severity		
Gauge to IEC 60947-1 / UL 94 flammability rating		
Approvals		
Clamped conductors		
Solid / Stranded	mm ²	
Flexible / Flexible with ferrule	mm ²	
Stripping length / Blade size		
Note		
Ordering data		
Version		
	500 V AC/DC. without LED	
	10-36 V AC/DC. with LED	
	30-70 V AC/DC. with LED	
	60-150 V AC/DC. with LED	
	100 - 250 V AC/DC. with LED	
Note		
Accessories		
Plug-in cross-connection		
	2-pole	
	10-pole	
End plate		
	dark beige	
Test plug		
Terminal blocks identical in contour		
Screwdriver		
	Standard	
Marking tags		
G-fuse cartridge. 5 x 20 mm (IEC 60127-2)		
	0.25 A fast	
	0.50 A fast	
	1.00 A fast	
	2.00 A fast	
For detailed information on other accessories and application in the online catalogue		

6.1 x 78 x 67.5			
6.3 / 4			
0.75...4			
			
II 3 G Ex Ex ec IIC Gc			
IEC	UL	CSA	EN 60079-7
500			440
6.3			6.3
4			4
	10kA		
	4 kV / 3		
	A4 / V-0		
CE CB CB CB CB TÜV24ATEX9191U			
Rated connection			
0.75...6 / 0.75...6			
0.75...6 / 0.75...4			
12 / 0.6 x 3.5 mm			


Type	Qty.	Order No.
SFS 4 2C BK	50	2941480000
SFS 4 2C 10-36V BK	50	2941490000
SFS 4 2C 30-70V BK	50	2941500000
SFS 4 2C 60-150V BK	50	2941510000
SFS 4 2C 100-250V BK	50	2941520000

Type	Qty.	Order No.
ZQV 4N/2	32 A 60	1527930000
ZQV 4N/10	32 A 20	1528090000
SEP 3C 4	20	2874800000
PS 2.0 MC	20	0310000000
A3C 4	32 A 50	2051240000
A3C 4 PE	50	2051410000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/6 PLUS MC NE WS	1000	1011320000
WS 10/6 M PLUS MC NE WS	600	2003780000
DEK 5/6 MM WS	600	2007120000
WS 8/6 MM WS	600	2007160000
G 20/0.25A/F	0.25 A 10	0430500000
G 20/0.50A/F	0.5 A 10	0430600000
G 20/1.00A/F	1 A 10	0430700000
G 20/2.00A/F	2 A 10	0430900000

SPGTB 2.5 FT 2C/1

2.5 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²

Max. clamping range

mm²

5.1 x 58.5 x 38

24 / 4

0.14...4



Technical data

Rated data	
Rated voltage of feed-through terminal	V
Rated current	A
for wire cross-section	mm ²
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Number of operating cycles	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-

Note

Based on IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
24			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Ordering data

Version	Type	Qty.	Order No.
dark beige Blue Orange Yellow/Green	SPGTB 2.5 FT 2C/1	100	3051460000
	SPGTB 2.5 FT 2C/1 BL	100	3051470000
	SPGTB 2.5 FT 2C/1 OR	50	3051480000
Note			

Accessories


Plug-in cross-connection	Type	Qty.	Order No.
2-pole 10-pole	ZQV 2.5N/2	24 A 60	1527540000
	ZQV 2.5N/10	24 A 20	1527690000
End plate			
dark beige	SEP 2C 2.5	20	2751080000
End bracket			
dark beige, screwable dark beige, direct mounting	AEB 35 SC/1	50	1991920000
	AEB 35 SCL/1 V0	20	2661280000
Test plug			
	SPG 2.5/1	24 A 50	3030250000
	SPG 2.5/10	24 A 20	3030100000
	SPG 2.5 L	24 A 50	3030160000
	SPG 2.5 MI	24 A 50	3030090000
	SPG 2.5 R	24 A 50	3030190000
Screwdriver			
Standard	SDIL 0.6X3.5X100	1	2749140000
Marking tags			
	DEK 5/5 PLUS MC NE WS	1000	1854490000
	DEK 5/5 MM WS	800	2007110000
	WS 8/5 MM WS	800	2007150000
	WS 10/5 M PLUS MC NE WS	600	2003770000

For detailed information on other accessories and application in the online catalogue

SPGTB 2.5 PE 2C/1

2.5 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²


Max. clamping range

mm²

5.1 x 58.5 x 38

/ 4

0.14...4



Technical data

IEC	UL	CSA	EN 60079-7
800			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Ordering data

Type	Qty.	Order No.
SPGTB 2.5 PE 2C/1	50	3051550000

Accessories


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP 2C 2.5	20	2751080000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L GN	24 A 50	3030240000
SPG 2.5 MI GN	24 A 50	3030220000
SPG 2.5 R GN	24 A 50	3030210000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000

For detailed information on other accessories and application in the online catalogue

SPGTB 2.5 FT 3C/1

2.5 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²

Max. clamping range

mm²

5.1 x 71.5 x 38

24 / 4

0.14...4



Technical data

IEC	UL	CSA	EN 60079-7
800			
24			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Ordering data

Type	Qty.	Order No.
SPGTB 2.5 FT 3C/1	50	3051490000
SPGTB 2.5 FT 3C/1 BL	50	3051500000
SPGTB 2.5 FT 3C/1 OR	50	3051510000

Accessories


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP 3C 2.5	20	2751090000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L	24 A 50	3030160000
SPG 2.5 MI	24 A 50	3030090000
SPG 2.5 R	24 A 50	3030190000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000

For detailed information on other accessories and application in the online catalogue

SPGTB 2.5 PE 3C/1

2.5 mm²

SNAP IN



Width/Height/Depth

mm

max. current / max. cond. cross-section

A/mm²


Max. clamping range

mm²

5.1 x 71.5 x 38

/ 4

0.14...4



Technical data

IEC	UL	CSA	EN 60079-7
800			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection

0.5...2.5 / 0.5...4

0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Ordering data

Type	Qty.	Order No.
SPGTB 2.5 PE 3C/1	50	3051560000

Accessories

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP 3C 2.5	20	2751090000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L GN	24 A 50	3030240000
SPG 2.5 MI GN	24 A 50	3030220000
SPG 2.5 R GN	24 A 50	3030210000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000

For detailed information on other accessories and application in the online catalogue

52



53

SPGTB 2.5 FT 4C/2

2.5 mm²

SNAP IN

</

SPGTB 2.5 PE 4C/2		2.5 mm ²	
SNAP IN 			
			
5.1 x 92 x 38			
/ 4			
0.34...4			
			
Based on IEC 60947-7-2			
IEC	UL	CSA	EN 60079-7
800			
2.5			
	8 kV / 3		
	A3 / V-0		
			
Rated connection			
0.5...2.5 / 0.5...4			
0.5...4 / 0.5...2.5			
10 / 0.6 x 3.5 mm			
Type	Qty.	Order No.	
SPGTB 2.5 PE 4C/2	50	3051570000	
Type	Qty.	Order No.	
ZQV 2.5N/2	24 A 60	1527540000	
ZQV 2.5N/10	24 A 20	1527690000	
SEP PGTB 2.5 4C	20	3051580000	
AEB 35 SC/1	50	1991920000	
AEB 35 SCL/1 V0	20	2661280000	
SPG 2.5/1	24 A 50	3030250000	
SPG 2.5/10	24 A 20	3030100000	
SPG 2.5 L GN	24 A 50	3030240000	
SPG 2.5 MI GN	24 A 50	3030220000	
SPG 2.5 R GN	24 A 50	3030210000	
SDIL 0.6X3.5X100	1	2749140000	
DEK 5/5 PLUS MC NE WS	1000	1854490000	
DEK 5/5 MM WS	800	2007110000	
WS 8/5 MM WS	800	2007150000	
WS 10/5 M PLUS MC NE WS	600	2003770000	

SPGTB 2.5 2T 4C/2

2.5 mm²

SNAP IN

2: 5.1 x 96 x 51.7

24 / 4

0.34...4

Based on IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
24			
2.5			
	8 kV / 3		
	A3 / V-0		

CE

UL

IEC

Rated connection



0.5...2.5 / 0.5...4



0.5...4 / 0.5...2.5

10 / 0.6 x 3.5 mm

Type	Qty.	Order No.
SPGTB 2.5 2T 4C/2	50	3051860000
SPGTB 2.5 2T 4C/2 BL	50	3051870000
SPGTB 2.5 2T 4C/2 OR	50	3051880000


Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP 2T 2.5	20	2913480000
SEP 2T 2.5 BL	20	2913490000
AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000
SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L	24 A 50	3030160000
SPG 2.5 MI	24 A 50	3030090000
SPG 2.5 R	24 A 50	3030190000
SDIL 0.6X3.5X100	1	2749140000
DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

SPGTB 2.5 2T VL 4C/2				2.5 mm ²
SNAP IN 				
				
5.1 x 96 x 51.7				
24 / 4				
0.34...4				
				
Based on IEC 60947-7-1				
IEC	UL	CSA	EN 60079-7	
800				
24				
2.5				
	8 kV / 3			
	A3 / V-0			
				
Rated connection				
0.5...2.5 / 0.5...4				
0.5...4 / 0.5...2.5				
10 / 0.6 x 3.5 mm				
Type	Qty.	Order No.		
SPGTB 2.5 2T VL 4C/2	50	3051890000		
SPGTB 2.5 2T VL 4C/2 BL	50	3051900000		
Type	Qty.	Order No.		
ZQV 2.5N/2	24 A 60	1527540000		
ZQV 2.5N/10	24 A 20	1527690000		
SEP 2T 2.5	20	2913480000		
SEP 2T 2.5 BL	20	2913490000		
AEB 35 SC/1	50	1991920000		
AEB 35 SCL/1 V0	20	2661280000		
SPG 2.5/1	24 A 50	3030250000		
SPG 2.5/10	24 A 20	3030100000		
SPG 2.5 L	24 A 50	3030160000		
SPG 2.5 MI	24 A 50	3030090000		
SPG 2.5 R	24 A 50	3030190000		
SDIL 0.6X3.5X100	1	2749140000		
DEK 5/5 PLUS MC NE WS	1000	1854490000		
DEK 5/5 MM WS	800	2007110000		
WS 8/5 MM WS	800	2007150000		
WS 10/5 M PLUS MC NE WS	600	2003770000		
SNAPMARK I	50	1805880000		

SPGTB 2.5 2T FT-PE 4C/2		2.5 mm²	
SNAP IN 			
			
5.1 x 96 x 51.7			
24 / 4			
0.34...4			
			
Based on IEC 60947-7-1			
IEC	UL	CSA	EN 60079-7
800			
24			
2.5			
	8 kV / 3		
	A3 / V-0		
			
Rated connection			
0.5...2.5 / 0.5...4			
0.5...4 / 0.5...2.5			
10 / 0.6 x 3.5 mm			
Type	Qty.	Order No.	
SPGTB 2.5 2T FT-PE 4C/2	50	3051910000	
Type	Qty.	Order No.	
ZQV 2.5N/2	24 A 60	1527540000	
ZQV 2.5N/10	24 A 20	1527690000	
SEP 2T 2.5	20	2913480000	
SEP 2T 2.5 BL	20	2913490000	
AEB 35 SC/1	50	1991920000	
AEB 35 SCL/1 V0	20	2661280000	
SPG 2.5/1	24 A 50	3030250000	
SPG 2.5/10	24 A 20	3030100000	
SPG 2.5 L	24 A 50	3030160000	
SPG 2.5 MI	24 A 50	3030090000	
SPG 2.5 R	24 A 50	3030190000	
SDIL 0.6X3.5X100	1	2749140000	
DEK 5/5 PLUS MC NE WS	1000	1854490000	
DEK 5/5 MM WS	800	2007110000	
WS 8/5 MM WS	800	2007150000	
WS 10/5 M PLUS MC NE WS	600	2003770000	
SNAPMARK I	50	1805880000	


SPGTB 2.5 2T PE 4C/2	2.5 mm ²
----------------------	---------------------

SNAP IN



Width/Height/Depth	mm
max. current / max. cond. cross-section	A/mm ²
Max. clamping range	mm ²

5.1 x 96 x 51.7	
/ 4	
0.14...4	



Technical data

Rated data	
Rated voltage of feed-through terminal	V
Rated current	A
for wire cross-section	mm ²
Rated impulse withstand voltage / Pollution severity	
Gauge to IEC 60947-1 / UL 94 flammability rating	
Number of operating cycles	
Approvals	
Clamped conductors	
Solid / Stranded	mm ²
Flexible / Flexible with ferrule	mm ²
Stripping length / Blade size	mm/-
Note	

Based on IEC 60947-7-2


IEC	UL	CSA	EN 60079-7
800			
2.5		8 kV / 3	
		A3 / V-0	




Rated connection	
0.5...2.5 / 0.5...4	
0.5...4 / 0.5...2.5	
10 / 0.6 x 3.5 mm	

SPGTB 2.5 2T 6C/2	2.5 mm ²
-------------------	---------------------

SNAP IN



5.1 x 115 x 52	
/ 4	
0.14...4	



Based on IEC 60947-7-2

IEC	UL	CSA	EN 60079-7
800			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection	
0.5...2.5 / 0.5...4	
0.5...4 / 0.5...2.5	
10 / 0.6 x 3.5 mm	

Ordering data

Version	
	dark beige
	Blue
	Orange
	Yellow/Green
Note	

Type	Qty.	Order No.
SPGTB 2.5 2T PE 4C/2	50	3051920000

Type	Qty.	Order No.
SPGTB 2.5 2T 6C/2	50	3096130000
SPGTB 2.5 2T 6C/2 BL	50	3096150000

Accessories

Plug-in cross-connection	
	2-pole
	10-pole
End plate	
	dark beige
End bracket	
	dark beige, screwable
	dark beige, direct mounting
Test plug	
Screwdriver	
	Standard
Marking tags	

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP 2T 2.5	20	2913480000

AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L GN	24 A 50	3030240000
SPG 2.5 MI GN	24 A 50	3030220000
SPG 2.5 R GN	24 A 50	3030210000

SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------

DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP PGTB 2T 2.5 6C	20	3096200000

AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L	24 A 50	3030160000
SPG 2.5 MI	24 A 50	3030090000
SPG 2.5 R	24 A 50	3030190000


SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------

DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000


For detailed information on other accessories and application in the online catalogue

SPGTB 2.5 2T 6C/2 VL	2.5 mm ²
----------------------	---------------------

SNAP IN



5.1 x 115 x 52	
24 / 4	
0.34...4	



Based on IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
24			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection	
0.5...2.5 / 0.5...4	
0.5...4 / 0.5...2.5	
10 / 0.6 x 3.5 mm	

Type	Qty.	Order No.
SPGTB 2.5 2T 6C/2 VL	50	3096160000
SPGTB 2.5 2T 6C/2 VL BL	50	3096170000

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP PGTB 2T 2.5 6C	20	3096200000

AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000


SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L	24 A 50	3030160000
SPG 2.5 MI	24 A 50	3030090000
SPG 2.5 R	24 A 50	3030190000

SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------


DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

SPGTB 2.5 2T 6C/2 FT-PE	2.5 mm ²
-------------------------	---------------------

SNAP IN



5.1 x 115 x 52	
24 / 4	
0.34...4	



Based on IEC 60947-7-1

IEC	UL	CSA	EN 60079-7
800			
24			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection	
0.5...2.5 / 0.5...4	
0.5...4 / 0.5...2.5	
10 / 0.6 x 3.5 mm	

Type	Qty.	Order No.
SPGTB 2.5 2T 6C/2 FT-PE	50	3096180000

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP PGTB 2T 2.5 6C	20	3096200000

AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000


SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L	24 A 50	3030160000
SPG 2.5 MI	24 A 50	3030090000
SPG 2.5 R	24 A 50	3030190000

SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------


DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

SPGTB 2.5 2T 6C/2 PE	2.5 mm ²
----------------------	---------------------

SNAP IN



5.1 x 115 x 52	
/ 4	
0.14...4	



Based on IEC 60947-7-2

IEC	UL	CSA	EN 60079-7
800			
2.5		8 kV / 3	
		A3 / V-0	



Rated connection	
0.5...2.5 / 0.5...4	
0.5...4 / 0.5...2.5	
10 / 0.6 x 3.5 mm	

Type	Qty.	Order No.
SPGTB 2.5 2T 6C/2 PE	50	3096190000

Type	Qty.	Order No.
ZQV 2.5N/2	24 A 60	1527540000
ZQV 2.5N/10	24 A 20	1527690000
SEP PGTB 2T 2.5 6C	20	3096200000


AEB 35 SC/1	50	1991920000
AEB 35 SCL/1 V0	20	2661280000

SPG 2.5/1	24 A 50	3030250000
SPG 2.5/10	24 A 20	3030100000
SPG 2.5 L GN	24 A 50	3030240000
SPG 2.5 MI GN	24 A 50	3030220000
SPG 2.5 R GN	24 A 50	3030210000

SDIL 0.6X3.5X100	1	2749140000
------------------	---	------------

DEK 5/5 PLUS MC NE WS	1000	1854490000
DEK 5/5 MM WS	800	2007110000
WS 8/5 MM WS	800	2007150000
WS 10/5 M PLUS MC NE WS	600	2003770000
SNAPMARK I	50	1805880000

Spring connection with SNAP IN technology (S-Series)
Pluggable terminal blocks

	APGTB 2.5 FT 4C/4	2.5 mm ²
Width/Height/Depth mm max. current / max. cond. cross-section A/mm² Max. clamping range mm²	 5.1 x 87 x 36.5 24 / 2.5 0.34...2.5	

Technical data

Rated data		IEC	UL	CSA	EN 60079-7
Rated voltage of feed-through terminal	V	800	600	600	
Rated current	A	24	20	20	
for wire cross-section	mm ²	2.5	AWG 28...12	AWG 28...12	
Rated impulse withstand voltage / Pollution severity				10kA	
Gauge to IEC 60947-1 / UL 94 flammability rating				6 kV / 3	
Number of operating cycles				A3 / V-0	
Approvals					
   					
Clamped conductors		Rated connection			
Solid / Stranded	mm ²	0.5...2.5 / 0.5...4			
Flexible / Flexible with ferrule	mm ²	0.5...2.5 / 0.5...2.5			
Stripping length / Blade size	mm/-	10 / 0.6 x 3.5 mm			
Note					

Ordering data

Version
dark beige
Blue
Orange

Accessories

Plug-in cross-connection	2-pole 10-pole 2-pole 10-pole
End plate	dark beige
End bracket	dark beige, screwable dark beige, direct mounting
Test plug	
Screwdriver	Standard
Marking tags	

For detailed information on other accessories and application in the online catalogue

APGTB 2.5 FT 4C/4 **2.5 mm²**



5.1 x 87 x 36.5

24 / 2.5

0.34...2.5


Technical drawing showing the side and top views of the APTB 2.5 FT 4C/4 terminal block. The side view shows the internal wiring channels and the mounting feet. The top view shows the terminal positions and the overall dimensions. The dimensions are 5.1 x 87 x 36.5 mm. The bottom view shows the terminal spacing, with a total length of 87 mm and individual terminal widths of 2.5 mm.

IEC 60947-7-1			
IEC	UL	CSA	EN 60079-7
800	600	600	
24	20	20	
2.5	AWG 28...12	AWG 28...12	
10kA			
6 kV / 3			
A3 / V-0			
   			
Rated connection			
0.5...2.5 / 0.5...4			
0.5...2.5 / 0.5...2.5			
10 / 0.6 x 3.5 mm			


Type	Qty.	Order No.
APGTB 2.5 FT 4C/4	100	2898150000
APGTB 2.5 FT 4C/4 BL	100	2898160000

Type		Qty.	Order No.
ZQV 2.5N/2	24 A	60	1527540000
ZQV 2.5N/10	24 A	20	1527690000
AEP PGTB 2.5 4C/4		20	2898190000
AEB 35 SC/1		50	1991920000
AEB 35 SCL/1 V0		20	2661280000
SDIL 0,6X3,5X100		1	2749140000
DEK 5/5 PLUS MC NE WS		1000	1854490000
DEK 5/5 MM WS		800	2007110000
WS 8/5 MM WS		800	2007150000
WS 10/5 M PLUS MC NE WS		600	2003770000

APGTB 2.5 PE 4C/4 **2.5 mm²**



5.1 x 77.5 x 36.5
/ 2.5
0.34...2.5



IEC 60947-7-1		
IEC	UL	CSA
800	600	600
EN 60079-7		
2.5	AWG 28...12	AWG 28...12
10kA		
6 kV / 3		
A3 / V-0		
   		
Rated connection		
0.5...2.5 / 0.5...4		
0.5...2.5 / 0.5...2.5		
10 / 0.6 x 3.5 mm		

Type	Qty.	Order No.
APGTB 2.5 PE 4C/4	50	2898170000


Type		Qty.	Order No.
ZQV 2.5N/2	24 A	60	1527540000
ZQV 2.5N/10	24 A	20	1527690000
AEP PGTB 2.5 4C/4		20	2898190000
AEB 35 SC/1		50	1991920000
AEB 35 SCL/1 VO		20	2661280000
SDIL 0,6X3,5X100		1	2749140000
DEK 5/5 PLUS MC NE WS		1000	1854490000
DEK 5/5 MM WS		800	2007110000
WS 8/5 MM WS		800	2007150000
WS 10/5 M PLUS MC NE WS		600	2003770000

Spring connection with SNAP IN technology (S-Series)
Pluggable terminal blocks

SPG 2.5...

2.5 mm²

SNAP IN



5.1 x 42.5 x 16.5

24 / 2.5

0.5...2.5

IEC	UL	CSA	EN 60079-7
800			
24			
2.5			
	8 kV / 3		
	A3 / V-0		
CE			
Rated connection		Steckanschluss	
0.5...2.5 / 0.5...2.5			
0.5...2.5 / 0.5...2.5			
10 / 0.6 x 3.5 mm			

Type	Qty.	Order No.
SPG 2.5/1	50	3030250000
SPG 2.5/2	40	3030170000
SPG 2.5/3	30	3030200000
SPG 2.5/4	20	3030150000
SPG 2.5/5	20	3030130000
SPG 2.5/6	40	3030140000
SPG 2.5/7	30	3030110000
SPG 2.5/8	30	3030120000
SPG 2.5/9	25	3030180000
SPG 2.5/10	20	3030100000
SPG 2.5/4-3BG-GN	20	3030230000
SPG 2.5/3-BG-BL-GN	30	3030270000
SPG 2.5/5-3BG-BL-GN	20	3030280000


Type	Qty.	Order No.
MCV SPG 2 5	50	3032900000

APGCE	50	1514490000
APGPC 2.5	50	1514500000

APGLE 2.5/4	25	2457570000
APGSR 2.5/4	25	2457580000


APGSR 2.5/4 - 4P	25	2457590000
APGSR 2.5/4 - 8P	25	2457600000
DEK 5/5 PLUS MC NE WS	1000	1854490000

WS 8/5 MM WS	800	2007150000
WS 10/5 M MC NE WS	720	1792000000



Single plates for individual assembly

The individual plates increase flexibility by providing a solution for every task. The plug-in connector is assembled directly onsite in line with application requirements. Each individual plate is available in green (GN) and beige (BE).



Plugs

SPG 2.5



Order data	Type	Qty.	Order No.
Single plate			
Start plate	SPG 2.5 L	20	3030160000
	SPG 2.5 L BL	20	3030290000
	SPG 2.5 L GN	20	3030240000
Middle plate	SPG 2.5 MI	20	3030090000
	SPG 2.5 MI BL	20	3030260000
	SPG 2.5 MI GN	20	3030220000
End plate	SPG 2.5 R	20	3030190000
	SPG 2.5 R BL	20	3030300000
	SPG 2.5 R GN	20	3030210000
Cover	MCV SPG 2.5	20	3032900000
Note			

Protective cover

- APGPC finger guard, also protects the contact point from dirt

APGPC


Protective cover



Ordering data
1.5 mm ²
2.5 mm ²
4.0 mm ²
6.0 mm ²
Hinweis

Type	Qty.	Order No.
APGPC 2.5	50	1514500000

Application




Coding elements

- For specific coding of the plug-in stations
- Protection against accidental mistake ensures process reliability

APGCE

Coding elements



Ordering data
2.5 mm ²
Note

Type	Qty.	Order No.
APGCE	50	1514490000

Application



Locking elements

- APGLE to interlock with the terminal block
- APGLE interlock, plug – socket

APGLE

Locking elements



Ordering data
2.5 mm ² / 4 mm ²
Note

Type	Qty.	Order No.
APGLE 2.5/4	25	2457570000

Application



Strain reliefs

- APGSR Strain relief transmits mechanical forces to the plastic housing and protects the contact point

APGSR


Strain reliefs




Ordering data
2.5 mm ² / 4 mm ²
2.5 mm ² / 4 mm ²
2.5 mm ² / 4 mm ²
Note

Type	Qty.	Order No.
APGSR 2.5/4	25	2457580000
APGSR 2.5/4 - 4P	25	2457590000
APGSR 2.5/4 - 8P	25	2457600000


Application




Spring connection with PUSH IN technology (S-Series)
Overview



Type		Order No. beige	Order No. blue BL	Order No. orange OR	Order No. red RD
2.5 mm²	S2C 2.5	2674530000	2753940000	2875120000	3109200000
	S3C 2.5	2674540000	2753950000	2875130000	3109280000
	S4C 2.5	2674550000	2753960000	2875140000	3109360000
4 mm²	S2C 4	2874820000	2874830000	3023540000	3109440000
	S3C 4	2874840000	2874850000	3023550000	3109520000
	S4C 4	2874860000	2874870000	3023560000	3109600000



Type		Order No. yellow YL	Order No. green GN	Order No. white WT	Order No. black BK
2.5 mm²	S2C 2.5	3109230000	3109180000	3109220000	3109160000
	S3C 2.5	3109310000	3109260000	3109300000	3109240000
	S4C 2.5	3109390000	3109340000	3109380000	3109320000
4 mm²	S2C 4	3109470000	3109420000	3109460000	3109400000
	S3C 4	3109550000	3109500000	3109540000	3109480000
	S4C 4	3109630000	3109580000	3109620000	3109560000



Type		Order No. light grey LTGY	Order No. brown BR	Order No. violet VT
2.5 mm²	S2C 2.5	3112230000	3109170000	3109210000
	S3C 2.5	3112240000	3109250000	3109290000
	S4C 2.5	3112250000	3109330000	3109370000
4 mm²	S2C 4	3112280000	3109410000	3109450000
	S3C 4	3112260000	3109490000	3109530000
	S4C 4	3112270000	3109570000	3109610000

Weidmüller – Your partner in Smart Industrial Connectivity

As experienced experts we support our customers and partners around the world with products, solutions and services in the industrial environment of power, signal and data. We are at home in their industries and markets and know the technological challenges of tomorrow. We are therefore continuously developing innovative, sustainable and useful solutions for their individual needs. Together we set standards in Smart Industrial Connectivity.

We cannot guarantee that there are no mistakes in the publications or software provided by us to the customer for the purpose of making orders. We try our best to quickly correct errors in our printed media.

All orders are based on our general terms of delivery, which can be reviewed on the websites of our group companies where you place your order. On demand we can also send the general terms of delivery to you.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
32758 Detmold, Germany
T +49 5231 14-0
F +49 5231 14-292083
www.weidmueller.com

Personal support can
be found on our website:
www.weidmueller.com/contact

Made in Germany
October 2025 / TCTM