

UK Attestation of Conformity

Document No. **UKCA DE PT0101 2111126 001 ISSUE01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26
32758 Detmold, Germany**

Object of the declaration **A – Series / Feed-through terminal blocks**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

	Directive	
The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere)	SI 2016/1107	SI2019/696(Schedule25) SI 2020/1460

References to the relevant BSEN or EN designated standards used, or references to the specifications, in relation to which conformity is declared:

EN IEC 60079-0:2018
EN IEC 60079-7:2015/A1:2018

Issued certificates from Approved Bodies

Approved Body (name, address and number)	Description of intervention	Certificate
ExVeritas, Units 16-18, Abenbury Way, Wrexham Industrial Estate, Wrexham, United Kingdom LL13 9UZ. Approved Body # 2585	Surveillance of production process (UKCA Ex)	ExVeritas 21UKQAN0176
Dakra Certification UK Ltd; Stokenchurch House, Oxford Road, Stokenchurch, HP14 3SX Approved Body # 8505	Surveillance of production process (UKCA Ex)	DEKRA 21UKQANxxxx
TUV Rheinland UK Ltd Friars Gate (Third Floor), 1011 Stratford Road, Shirley, Solihull, B90 4BN Approved Body # 2571	UKEx-Type Examination UKCA	TÜV21UKEX7001U

Detmold, 14.03.2022
Ort, Datum / place, date


Rechtsverbindliche Unterschrift / legally binding signature

Name und Funktion / name and function

Arnd Schepmann, Business Unit Leiter Terminals

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observe.

UK Attestation of Conformity

Document No.

UKCA DE PT0101 2111126 001 ISSUE01

Object of the declaration

A2C 1.5	1552790000
A2C 1.5 BL	1552820000
A2C 1.5 OR	1552830000
A2C 1.5 RD	2508020000
A2C 1.5 WT	2508160000
A2C 1.5 BK	2508170000
A2C 1.5 DBL	2508180000
A2C 1.5 YL	2508190000
A2C 1.5 BR	2508200000
A2C 1.5 GN	2508210000
A2C 1.5 LTGY	2508220000
A2C 1.5 DL	2674590000
A2C 1.5 DL BL	2674600000
A3C 1.5 OR	1552780000
A3C 1.5 BL	1552770000
A3C 1.5	1552740000
A3C 1.5 BK	2534230000
A3C 1.5 GN	2534480000
A3C 1.5 LTGY	2534490000
A3C 1.5 RD	2534500000
A3C 1.5 WT	2534510000
A3C 1.5 YL	2534520000
A3C 1.5 BR	2534530000
A3C 1.5 DBL	2534540000
A3C 1.5 DL	2674630000
A3C 1.5 DL BL	2674640000
A4C 1.5	1552690000
A4C 1.5 BL	1552700000
A4C 1.5 OR	1552720000
A4C 1.5 BK	2534260000
A4C 1.5 GN	2534410000
A4C 1.5 LTGY	2534420000
A4C 1.5 RD	2534430000
A4C 1.5 WT	2534440000
A4C 1.5 YL	2534450000
A4C 1.5 BR	2534460000
A4C 1.5 DBL	2534470000
A4C 1.5 DL	2674660000
A4C 1.5 DL BL	2674670000
A2C 2.5	1521850000
A2C 2.5 BL	1521880000
A2C 2.5 OR	1521930000
A2C 2.5 GN	1521950000
A2C 2.5 LTGY	2003110000
A2C 2.5 WT	1521970000
A2C 2.5 YL	1521940000
A2C 2.5 BK	1521980000

UK Attestation of Conformity

A2C 2.5 RD	1521900000
A2C 2.5 BR	2508030000
A2C 2.5 DBL	2508000000
A2C 2.5 /DT/FS	1989900000
A2C 2.5 /DT/FS BL	1989910000
A2C 2.5 /DT/FS OR	1989920000
A2C 2.5 DL	2674690000
A2C 2.5 DL BL	2674700000
A2C 2.5 DL mit AP	7690001590

A3C 2.5	1521740000
A3C 2.5 BL	1521780000
A3C 2.5 OR	1521830000
A3C 2.5 WT	1521890000
A3C 2.5 GN	1521870000
A3C 2.5 LTGY	2003120000
A3C 2.5 DBL	2534690000
A3C 2.5 BR	2534730000
A3C 2.5 YL	1521840000
A3C 2.5 RD	1521800000
A3C 2.5 BK	1521920000
A3C 2.5 DL	2674720000
A3C 2.5 DL BL	2674730000

A4C 2.5	1521690000
A4C 2.5 BL	1521700000
A4C 2.5 OR	1521720000
A4C 2.5 LTGY	2003130000
A4C 2.5 YL	1521730000
A4C 2.5 BK	1521820000
A4C 2.5 WT	1521790000
A4C 2.5 RD	1521710000
A4C 2.5 GN	2003130000
A4C 2.5 DBL	2534740000
A4C 2.5 BR	2534750000
A4C 2.5 DL	2674750000
A4C 2.5 DL BL	2674700000

A2C 4	2051180000
A2C 4 BL	2051210000
A2C 4 OR	2051230000
A2C 4 LTGY	2051330000
A2C 4 BR	2534370000
A2C 4 DBL	2534380000
A2C 4 RD	2051220000
A2C 4 WT	2051290000
A2C 4 GN	2051260000
A2C 4 YL	2051250000
A2C 4 BK	2051310000
A2C 4 DL	2674780000
A2C 4 DL BL	2674790000
A2C 4 DL mit AP	7690001606

A3C 4	2051240000
A3C 4 BL	2051280000
A3C 4 OR	2051320000
A3C 4 GN	2051350000
A3C 4 YL	2051340000

UK Attestation of Conformity

A3C 4 RD	2051300000
A3C 4 LTGY	2051460000
A3C 4 BR	2534290000
A3C 4 DBL	2534360000
A3C 4 WT	2051370000
A3C 4 BK	2051400000
A3C 4 DL	2674810000
A3C 4 DL BL	2674820000
A4C 4	2051500000
A4C 4 BL	2051520000
A4C 4 OR	2051540000
A4C 4 BR	2534390000
A4C 4 DBL	2534400000
A4C 4 YL	2051550000
A4C 4 GN	2051580000
A4C 4 RD	2051530000
A4C 4 LTGY	2051670000
A4C 4 WT	2051610000
A4C 4 BK	2051660000
A4C 4 DL	2674840000
A4C 4 DL BL	2674850000
A2C 6	1992110000
A2C 6 BL	1991790000
A2C 6 OR	1991800000
A2C 6 DL	2674870000
A2C 6 DL BL	2674880000
A3C 6	1991820000
A3C 6 BL	1991830000
A3C 6 OR	1991840000
A3C 6 DL	2674900000
A3C 6 DL BL	2674920000
ALO 6	1991780000
ALO 6 BL	2065120000
A2C 10	2490360000
A2C 10 BL	2490370000
A2C 10 DL	2674940000
A2C 10 DL BL	2674950000
A2C 10 OR	2697900000
A3C 10	2490520000
A3C 10 BL	2490510000
A3C 10 DL	2674970000
A3C 10 DL BL	2674980000
A2C 16	2494000000
A2C 16 BL	2494100000
A2C 16 DL	2675000000
A2C 16 DL BL	2675010000
A3C 16	2494090000
A3C 16 BL	2494080000
A3C 16 DL	2675030000
A3C 16 DL BL	2675040000

UK Attestation of Conformity

A3C 16 DL mit AP	7690001596
ALO 16	2502280000
ALO 16 BL	2502320000
A2C 35	2551510000
A2C 35 BL	2552090000
A2C 35 FE	2551530000
A2C 35 3FT	2552100000
A2C 35 3FT-N	2552130000
A2C 35 3FT-FE	2552110000
A2C 35 3FT-N-FE	2552140000
A2C 35 DM	2551550000
A2C 35 BL DM	2552150000
A2C 35 FE DM	2552160000
A2C 35 3FT DM	2552170000
A2C 35 3FT-N DM	2552190000
A2C 35 3FT-FE DM	2552180000
A2C 35 3FT-N-FE DM	2552200000
A2C 35 DL	2742060000
A2C 35 FE DL	2742070000
A2C 35 DL BL	2755890000
A2C 35 3FT-N	2552130000
A2C 35 3FT	2552100000
A2C 35 3FT-N-FE-DM	2552200000
A2C 35 3FT-N-DM	2552190000
A2C 35 3FT-FE-DM	2552180000
A2C 35 3FT-DM	2552170000
A2C 35 3FT-N-FE	2552140000
A2C 35 3FT-FE	2552110000
A2T 1.5	2469370000
A2T 1.5 BL	2471430000
A2T 1.5 OR	2471440000
A2T 1.5 DL	2675060000
A2T 1.5 DL BL	2675070000
A2T 1.5 KNX RD-BK	2652200000
A2T 1.5 KNX WT-YL	2652210000
A2T 1.5 VL	2469400000
A2T 1.5 VL BL	2471450000
A2T 1.5 VL OR	2471460000
A2T 1.5 VL DL	2675090000
A2T 2.5	1547610000
A2T 2.5 BL	1547620000
A2T 2.5 OR	1547630000
A2T 2.5 N-FT	2723370000
A2T 2.5 SNAPMARK	2581250000
A2T 2.5 SNAPMARK BL	2581280000
A2T 2.5 DL	2675110000
A2T 2.5 DL BL	2675120000
A2T 2.5 DL mit AP	7690001607
A2T 2.5 VL	1547650000
A2T 2.5 VL BL	1547660000
A2T 2.5 VL OR	1547670000

UK Attestation of Conformity

A2T 2.5 VL DL	2675140000
A2T 2.5 3C	2531290000
A2T 2.5 3C BL	2531510000
A2T 2.5 3C N-FT	2736830000
A2T 2.5 3C FT BK-FT	2766890000
A2T 2.5 3C VL	2531310000
A2T 2.5 3C VL BL	2531530000
A2T 4	2539970000
A2T 4 BL	2540040000
A2T 4 OR	2552480000
A2T 4 N-FT	2724450000
A2T 4 DL	2675160000
A2T 4 DL BL	2675170000
A2T 4 VL	2540020000
A2T 4 VL BL	2540030000
A2T 4 VL OR	2552590000
A2T 4 VL DL	2675190000
A3T 2.5	2428510000
A3T 2.5 BL	2428520000
A3T 2.5 DL	2771890000
A3T 2.5 VL	2428540000
A3T 2.5 VL BL	2428850000
A3T 2.5 VL DL	2735510000
A3T 2.5 VL DL mit AP	7690001593
AMC 2.5	2434340000
AMC 2.5 800V	2434370000
AMC 2.5 DL	2742040000
AMC 2.5 800V DL	2742050000
A2C 95/120	2694060000
A2C 95/120 BL	2694070000
A2C 95/120 FE	2694080000
A2C 95/120 3FT-N-FE	2694100000
A2C 95/120 3FT-N	2694120000
A2C 95/120 3FT-FE	2694130000
A2C 95/120 3FT	2694140000
A2C 95/120-DM	2694150000
A2C 95/120 BL-DM	2694160000
A2C 95/120 FE-DM	2694170000
A2C 95/120 3FT-N-FE-DM	2694180000
A2C 95/120 3FT-N-DM	2694200000
A2C 95/120 3FT-FE-DM	2694220000
A2C 95/120 3FT-DM	2694230000
A2C 95/120 DL	2742120000
A2C 95/120 FE DL	2742130000
A2C 95/120 DL BL	2755910000
A2C 50/70	2663250000
A2C 50/70 BL	2663260000
A2C 50/70 FE	2663270000
A2C 50/70 3FT-N-FE	2663290000

UK Attestation of Conformity

A2C 50/70 3FT-N	2663300000
A2C 50/70 3FT-FE	2663310000
A2C 50/70 3FT	2663320000
A2C 50/70-DM	2663330000
A2C 50/70 BL-DM	2663340000
A2C 50/70 FE-DM	2663350000
A2C 50/70 3FT-N-FE-DM	2663360000
A2C 50/70 3FT-N-DM	2663370000
A2C 50/70 3FT-FE-DM	2663380000
A2C 50/70 3FT-DM	2663390000
A2C 50/70 DL	2742090000
A2C 50/70 FE DL	2742100000
A2C 50/70 DL BL	2755900000