



Type Approval Certificate

This is to certify that the undernoted product(s) has/have been tested with satisfactory results in accordance with the relevant requirements of the Lloyd's Register Type Approval System.

Manufacturer	Weidmueller Interface GmbH & Co. KG
Address	Klingenbergstr. 26, Detmold, 32758, Germany
Place of Production	Weidmüller Lanškroun s.r.o. Dobrovského 1115, Lanškroun, 563 01, Czech Republic
Place of Production	EWE s.r.o. Třebovská 570, Ústí nad Orlicí, 562 03, Czech Republic
Place of Production	Weidmüller Interface GmbH & Co. KG Klingenbergstrasse 16, Detmold, 32758, Germany
Type	Terminals/Insulators
Description	Feed through terminal blocks for rail mounting with recessed screw connectors insulation material: Wemid and Pa 6,6 in all colours.
Trade Name	WDU 2.5/1.5 ZR, WDU 70/95, WDU 120/150
Application	Marine, offshore and industrial applications for use in environmental categories ENV1, ENV2, ENV3 and ENV4 as defined in Lloyd's Register's Type Approval System, Test Specification Number 1 - 2002.

71 Fenchurch Street, London, EC3M 4BS, United Kingdom

Thorsten Wolff

Senior Specialist to Lloyd's Register EMEA
A member of the Lloyd's Register group

Lloyd's Register Group Limited, its affiliates and subsidiaries and their respective officers, employees or agents are, individually and collectively, referred to in this clause as 'Lloyd's Register'. Lloyd's Register assumes no responsibility and shall not be liable to any person for any loss, damage or expense caused by reliance on the information or advice in this document or howsoever provided, unless that person has signed a contract with the relevant Lloyd's Register entity for the provision of this information or advice and in that case any responsibility or liability is exclusively on the terms and conditions set out in that contract.



Type Approval Certificate

Specified Standard IEC 60947-7-1: 04.2009

Ratings	Types	Voltage [V] AC	Current [A]	Conductor Size max [mm ²]
	WDU 2.5/1.5 ZR	690	24/17.5	2.5/1.5
	WDU 70/95	1000	232	95
	WDU 120/150	1000	269	120

This certificate is not valid for equipment, the design, ratings or operating parameters of which have been varied from the specimen tested. The manufacturer should notify Lloyd's Register EMEA of any modification or changes to the equipment in order to obtain a valid Certificate.

Previous Version: 89/20171 (E8)

The Design Appraisal Document HPC1762110-22/TW and its supplementary Type Approval Terms and Conditions form part of this Certificate.

71 Fenchurch Street, London, EC3M 4BS, United Kingdom

Lloyd's Register Group Limited, its affiliates and subsidiaries and their respective officers, employees or agents are, individually and collectively, referred to in this clause as 'Lloyd's Register'. Lloyd's Register assumes no responsibility and shall not be liable to any person for any loss, damage or expense caused by reliance on the information or advice in this document or howsoever provided, unless that person has signed a contract with the relevant Lloyd's Register entity for the provision of this information or advice and in that case any responsibility or liability is exclusively on the terms and conditions set out in that contract.