




Product Service

Attestation of Conformity

No. N8A 18 04 33299 390

Holder of Certificate: Weidmüller Interface GmbH & Co. KGKlingenbergstr. 16
32758 Detmold
GERMANY**Product:** Switching power supply unit
(Switching Power Supply)

This Attestation of Conformity is issued on a voluntary basis according to the Low Voltage Directive 2014/35/EU relating to electrical equipment designed for use within certain voltage limits. It confirms that the listed equipment complies with the principal protection requirements of the directive and is based on the technical specifications applicable at the time of issuance. It refers only to the particular sample submitted for testing and certification. See also notes overleaf.

Test report no.: 6821017057302**Date,** 2018-04-26
(Yager Bi)

CE After preparation of the necessary technical documentation as well as the EU conformity declaration the required CE marking can be affixed on the product. That declaration of conformity is issued under the sole responsibility of the manufacturer. Other relevant EU-directives have to be observed.

Page 1 of 2



Product Service

Attestation of Conformity
No. N8A 18 04 33299 390**Model(s):** PRO TOP1 72W 24V 3A, PRO TOP1 72W 24V 3A CO,
PRO TOP1 72W 24V 3A F**Brand:** Weidmüller**Parameters:**
Rated Input : 100-240VAC, 50/60Hz, 2-1A or
120-340VDC, 1.5-0.8A
Rated Output : 24VDC, 3A
Protection Class : I
Degree of Protection : IPX0
Remarks:
- When installing the equipment, all requirements of
the mentioned standard must be fulfilled.
- The maximum operating ambient temperature is 70°C.
Refer to the installation and operating instruction from
manufacturer for the details of loading condition and
operating ambient temperature.
- Clearance was evaluated for operating altitude up to
5000m above sea level.
- The AC input voltage tolerance is 85-277VAC; The DC
input voltage tolerance is 80-410VDC.
- It's built-in component, suitable enclosure should be
provided in end system.
- For spacing and insulation considerations, the DC input
of this power supply shall be derived from the end system
of maximum 240VAC mains supply.**Tested**
according to: EN 62368-1:2014/A11:2017