



Product Service

Attestation of Conformity

No. N8A 033299 0416 Rev. 00

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 16
32758 Detmold
GERMANY

Product: Switching power supply unit
(Switching Power Supply)

This Attestation of Conformity is issued on a voluntary basis according to the Low Voltage Directive 2014/35/EU relating to electrical equipment designed for use within certain voltage limits. It confirms that the listed equipment complies with the principal protection requirements of the directive and is based on the technical specifications applicable at the time of issuance.
It refers only to the particular sample submitted for testing and certification. See also notes overleaf.

Test report no.: 6821018045901

Date, 2018-10-11


(Yager Bi)

Page 1 of 2

After preparation of the necessary technical documentation as well as the EU declaration of conformity the required CE marking can be affixed on the product. The declaration of conformity is issued under the sole responsibility of the manufacturer. Other relevant EU-directives have to be observed.

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstraße 65 • 80339 Munich • Germany

TÜV®



Product Service

Attestation of Conformity

No. N8A 033299 0416 Rev. 00

Model(s): PRO TOP3 120W 24V 5A,
PRO TOP3 120W 24V 5A CO

Brand: Weidmüller

Weidmüller

Parameters:

Ratings: Input: 3x400-500VAC, 50/60Hz, 3x0.4-0.3A or 450VDC-500VDC, 0.4-0.3A
Output: 24VDC, 5A

Protection Class: I

Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating ambient temperature.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- When installing the equipment into end system, care must be taken that the output and associated wire(s) may not be touched.
- The input tolerance of the switching power supply is 3x320-575Vac or 450-800Vdc, and the DC input should be based on a rectifier bridge after AC mains supply.
- External 2A, min. 500VAC/DC non-time delayed fuse or breaker should be provided before each input (L1, L2, L3) of this power supply for protection when installed into the end system.

Tested EN 62368-1:2014/A11:2017
according to:

Page 2 of 2

After preparation of the necessary technical documentation as well as the EU declaration of conformity the required CE marking can be affixed on the product. The declaration of conformity is issued under the sole responsibility of the manufacturer. Other relevant EU-directives have to be observed.

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstraße 65 • 80339 Munich • Germany

TÜV®

ZERTIFIKAT ♦ CERTIFICATE ♦ 認證證書 ♦ CERTIFICADO ♦ CERTIFICAT