

Attestation of Conformity

No. N8A 033299 0418 Rev. 00

Holder of Certificate: Weidmüller Interface GmbH & Co. KG

Klingenbergstr. 16
32758 Detmold
GERMANY

Product: Switching power supply unit
(Switching Power Supply)

This Attestation of Conformity is issued on a voluntary basis according to the Low Voltage Directive 2014/35/EU relating to electrical equipment designed for use within certain voltage limits. It confirms that the listed equipment complies with the principal protection requirements of the directive and is based on the technical specifications applicable at the time of issuance. It refers only to the particular sample submitted for testing and certification. See also notes overleaf.

Test report no.: 6821018043301

Date, 2018-10-11

(Yager Bi)

Attestation of Conformity

No. N8A 033299 0418 Rev. 00

Model(s): PRO TOP3 240W 24V 10A,
PRO TOP3 240W 24V 10A CO

Brand: Weidmüller

Weidmüller 

Parameters:

Rated Input: 3x400-500VAC, 50/60Hz, 3x0.6-0.5A or 450-500VDC, 0.7-0.6A

Rated Output: 24VDC, 10A

Protection Class: I

Degree of Protection: IPX0

Remarks:

- When installing the equipment, all requirements of the mentioned standard must be fulfilled.
- Clearance was evaluated for operating altitude up to 5000m above sea level.
- Refer to the installation and operating instruction from manufacturer for the details of loading condition and operating ambient temperature.
- When installing the equipment into end system, care must be taken that the output and associated wire(s) may not be touched.
- Built-in type equipment, suitable enclosure and type of supply connection should be provided by end system.
- The input tolerance of the switching power supply is 3x320-575Vac or 450-800Vdc, and the DC input should be based on a rectifier bridge after AC mains supply.
- External 2-3A, min. 500VAC/DC non-time delayed fuse or breaker should be provided before each input (L1,L2,L3) of this power supply for protection when installed into the end system.

**Tested
according to:**

EN 62368-1:2014/A11:2017