

UK Attestation of Conformity

Document No. **UKCA DE PT0102 211125 002 ISSUE01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26
32758 Detmold, Germany**

Object of the declaration **A – Series / PE- terminal blocks**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

	Directive	
The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere)	SI 2016/1107	SI2019/696(Schedule25) SI 2020/1460

References to the relevant BSEN or EN designated standards used, or references to the specifications, in relation to which conformity is declared:

EN IEC 60079-0:2018
EN IEC 60079-7:2015/A1:2018

Issued certificates from Approved Bodies

Approved Body (name, address and number)	Description of intervention	Certificate
ExVeritas, Units 16-18, Abenbury Way, Wrexham Industrial Estate, Wrexham, United Kingdom LL13 9UZ. Approved Body # 2585	Surveillance of production process (UKCA Ex)	ExVeritas 21UKQAN0176
Dekra Certification UK Ltd; Stokenchurch House, Oxford Road, Stokenchurch, HP14 3SX Approved Body # 8505	Surveillance of production process (UKCA Ex)	DEKRA 21UKQANxxxx
TUV Rheinland UK Ltd Friars Gate (Third Floor), 1011 Stratford Road, Shirley, Solihull, B90 4BN Approved Body # 2571	UKEx-Type Examination UKCA	TÜV 21 UKEX 7001 U

Detmold, 14.03.2022
Ort, Datum / place, date

Name und Funktion / name and function


Rechtsverbindliche Unterschrift / legally binding signature

Arnd Schepmann, Business Unit Leiter Terminals

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observe.

UK Attestation of Conformity

Document No.

UKCA DE PT0102 2111255 002 ISSUE01

Object of the declaration

A2C 1.5 PE	1552680000
A2C 1.5 PE DL	2674610000
A3C 1.5 PE	1552670000
A3C 1.5 PE DL	2674650000
A4C 1.5 PE	1552660000
A4C 1.5 PE DL	2674680000
A2C 2.5 PE	1521680000
A2C 2.5 PE /DT/FS	1989890000
A2C 2.5 PE DL	2674710000
A2C 2.5 PE DL mit AP	7690001591
A2C 2.5 PE - WS 10/5	7690000579
A2C 2.5 FE	2690460000
A3C 2.5 PE	1521670000
A3C 2.5 PE DL	2674740000
A3C 2.5 PE DL mit AP	7690001592
A4C 2.5 PE	1521540000
A4C 2.5 PE DL	2674770000
A4C 2.5 PE - WS 10/5	7690000593
A4C 2.5 FE	2690470000
A2C 6 PE	1991810000
A2C 6 PE DL	2674890000
A2C 6 PE DL mit AP	7690001595
A2C 6 PE - WS 10/8	7690000585
A2C 6 FE	2734160000
A3C 6	1991820000
A3C 6 BL	1991830000
A3C 6 OR	1991840000
A3C 6 DL	2674900000
A3C 6 DL BL	2674920000
A3C 6 - WS 10/8	7690000586
A3C 6 BL - WS 10/8	7690000587
A2C 10 PE	2490440000
A2C 10 PE DL	2674960000
A2C 10 FE	2734170000
A3C 10 PE	2490590000
A3C 10 PE DL	2674990000
A2C 16 PE	2494010000
A2C 16 PE DL	2675020000
A2C 16 PE DL mit AP	7690001605
A2C 35 3FT-N-PE	2551540000
A2C 35 3FT-PE	2552120000

UK Attestation of Conformity

A3C 16 PE	2494020000
A3C 16 PE DL	2675050000
A2T 1.5 FT-PE	2469390000
A2T 1.5 FT-PE	2469390000
A2T 1.5 FT-PE DL	2675080000
A2T 1.5 PE	2469410000
A2T 1.5 PE DL	2675100000
A2T 2.5 PE	1547680000
A2T 2.5 PE DL	2675150000
A2T 2.5 FT-PE	1547640000
A2T 2.5 FT-PE DL	2675130000
A2T 2.5 3C FT-PE	2531300000
A2T 2.5 3C N-PE	2623550000
A2T 2.5 3C PE	2531320000
A2T 4 FT-PE	2539980000
A2T 4 FT-PE DL	2675180000
A2T 4 PE	2539990000
A2T 4 PE DL	2675200000
A3T 2.5 PE	2428550000
A3T 2.5 FT-FT-PE	2428530000
A3T 2.5 N-FT-PE	2428840000
A3T 2.5 FT-FT-PE DL	2757430000
A2C 95/120 PE	2694090000
A2C 95/120 PE DL	2742140000
A2C 50/70 PE	2663280000
A2C 50/70 PE DL	2742110000