

**INSTALLATION INSTRUCTIONS**  
**& CONDITIONS FOR SAFE USE**

II 2 GD

Ex eb IIC Gb

**Modular TERMINAL Blocks: Z- Series****DEMKO 15 ATEX 1467U**  
**IECEx ULD 15.0008U**  
**UL21UKEX2117U**

Standards:

EN IEC 60079-0:2018 and EN IEC 60079-7:2015 A1:2018  
IEC 60079-0: 7th Edition and IEC 60079-7: 5.1th Edition**Modular Terminal Blocks: ZDU/ZPE**

Version:	ZDU 4/4AN*	Order No 7904290000
----------	------------	------------------------

in conjunction with:	ZPE 4/4AN*	Order No 7904280000
----------------------	------------	------------------------

Accessories:	Type	Order No
end plate	ZAP/TW4/4AN*	7904210000
end bracket	ZEW 35*	9540000000

Terminal rail	TS 35/... acc.to DIN EN 60715
---------------	-------------------------------

Cross-connection	Plugable*	Order No
	ZQV 4/2 GE	1608950000
	ZQV 4/3 GE	1608960000
	ZQV 4/4 GE	1608970000
	ZQV 4/5 GE	1608980000
	ZQV 4/6 GE	1608990000
	ZQV 4/7 GE	1609000000
	ZQV 4/8 GE	1609010000
	ZQV 4/9 GE	1609020000
	ZQV 4/10 GE	1609030000

**Insulation material:**

- Type	Wemid
- Tracking resistance (A) to IEC 60112	CTI ≥ 600
- Flammability class to UL 94	V0
- Operating temperature range	-60°C...+110°C (insulating material limit)
- Ambient temperature range	-60°C...+40°C (for T6 applications)
- Ambient temperature range	-60°C...+55°C (for T5 applications)
- Ambient temperature range	-60°C...+70°C (for T4 applications)





\* in all colours

**Technical data according to IEC/EN 60079-7 (increased safety "eb"):**

	<b>ZDU 4/4AN</b>	<b>ZPE 4/4AN</b>
- Rated voltage	550 V	
- Rated current	28 A / $\Delta T$ 40 K	
- Temperature rise with rated current	$\leq 40$ K / 28 A	
- Rated current with ZQV	28 A / $\Delta T$ 40 K	
- Contact resistance with rated conductor, 4 mm <sup>2</sup>	0,7 m $\Omega$	0,7 m $\Omega$
- Rated conductor cross section	4 mm <sup>2</sup>	4 mm <sup>2</sup>
- Conductor cross section solid	0,5 - 6 mm <sup>2</sup>	0,5 - 6 mm <sup>2</sup>
- Conductor cross section stranded	0,5 - 6 mm <sup>2</sup>	0,5 - 6 mm <sup>2</sup>
- Conductor cross section flexible	0,5 - 6 mm <sup>2</sup>	0,5 - 6 mm <sup>2</sup>
- cross section, American Wire Gauge	26 - 10 AWG	26 - 10 AWG
- conductor cross section flexible with ferrule acc. to DIN 46228 part 1 + 4	0,5 - 4 mm <sup>2</sup>	0,5 - 4 mm <sup>2</sup>
- Stripping length	12 mm	12 mm

**IECEx / ATEX / UKCA Terminal and Cross-Connection Arrangements:**

Max voltage data according to IEC/EN 60079-7 in conjunction with protective earth terminal blocks of the ZPE-Series, (increased safety "eb"):

**Application Case****A - Continuous****C - Adjacent – separated by a end plate****D - Intermediate - bridging one or more unconnected terminals****E - Next to a protective conductor terminal (earth) without a end plate**

Information for further cross-connector arrangements will be provided on request.

**Note:**

If smaller cross sections than the rated cross section are used, the belonging lower current has to be laid down in the IECEx/EC-Type Examination Certificate of the complete apparatus.

**Mounting instructions:**

The ZDU/ZPE series is suitable for application in enclosures in atmospheres with flammable gases or combustible dust. For use in flammable gases these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-7. For use in combustible dust these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-31.

Regarding the use of accessories the instructions of the manufacturer must be followed.

**Schedule of Limitations:**

The ZDU/ZPE terminals are suitable for use in enclosures in atmospheres with flammable gases or combustible dust. For flammable gases these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-7. For combustible dust the enclosure must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-31.

The terminal blocks shall be placed inside a suitable IECEx/ATEX/UKCA certified IP54 enclosure for gas atmosphere. For dust atmosphere the terminal blocks shall be mounted inside a suitable IECEx/ATEX/UKCA certified 't' enclosure (IEC/EN60079-31).

Under normal operating conditions the temperature rise of the terminal blocks is maximum 40 K, measured at the maximum permitted rated current. Due to the above mentioned, the terminal blocks may be used in apparatus of temperature classes T6..T1 as long as the terminal block ambient temperature range is not exceeded. No part of terminal block must exceed 110 °C under any condition.

T6 (- 60°C ... +40 °C)

T5 (- 60°C ... +55 °C)

T4 (- 60°C ... +70 °C)

When using the types ZDU and ZPE especially with other terminal blocks series or sizes or accessories the requirements for clearance and creepage distances according to IEC/EN60079-7 must be observed. Regarding the use of covers, cross-connectors and end brackets the instructions of the manufacturer must be followed.

For cross connection accessories current rating, resistance across the terminal please refer to the table under "Technical data" above.

When using ferrules for flexible conductors, it must be ensured that the test requirements of DIN 46228-1 and DIN 46228-4 are complied with. Therefore we recommend the use of the appropriate Weidmüller crimping tools. The length of the copper ferrule must correspond to the specified stripping length.

No other wire sizes or types than the ones specified in instructions must be used. The terminal blocks must either be mounted next to another block of the same type and size or with an end plate.

If smaller conductor cross sections than the rated conductor cross sections are used, then the corresponding lower current shall be stated in the Certificate of the complete apparatus.



- Cross connections with blank ends shall not be used.
- Manually cut cross connections shall not be used.

**Essential Health and Safety Requirements:**

Concerning ESRs this Schedule verifies compliance with the Annex II of ATEX / Schedule 1 of UKCA directive and Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 only. By placing the product on the market, the manufacturer declares compliance with other relevant Directives, and all other safety related requirements including those of Annex II / Schedule 1 of these Directives.