

Document No. **UKCA DE PN4800 220301 004 ISS 01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26
32758 Detmold, Germany**

Object of the declaration **Industrial Ethernet managed Switches / SubstationLine**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

		Directive
☒ The Electrical Equipment (Safety) Regulations 2016	SI 2016/1101	SI2019/696(Schedule23) SI 2020/1460
☒ The Electromagnetic Compatibility Regulations 2016	SI 2016/1091	SI2019/696(Schedule20) SI 2020/1460
☐ The supply of Machinery (Safety) Regulations 2008	SI 2008/1597	SI2019/696(Schedule12) SI 2020/1460
☐ The Radio Equipment Regulations 2017	SI 2017/1206	SI2019/696(Schedule29) SI 2020/1460
☒ The Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment Regulations 2012 RoHS	SI 2012/3032	SI2019/188
☐ The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere)	SI 2016/1107	SI2019/696Schedule25) SI 2020/1460

Document No.

UKCA DE PN4800 220301 004 ISS 01

References to the relevant EN or BSEN designated standards used, or references to the specifications, in relation to which conformity is declared:

Safety - SI 2016/1101:
EN 62368-1:2014+A11:2017

EMC - SI 2016/1091:
EN 55032:2015+A11:2020
EN 55035:2017+A11:2020
EN 61000-3-2:2019
EN 61000-3-3:2013+A1:2019

RoHS - SI 2012/3032:
EN IEC 63000:2018

Object of the declaration (continued from page 1)

Article description:	Article no.
IE-SW-SL10M-7TX-3GC-HV	2778950000

Detmold, 01.03.2022
place, date

name and function


legally binding signature

Andreas Hoffmann
Vice President BU u-mation and Industrial Ethernet

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observe.