

UK Attestation of Conformity

Document No. **UKCA DE PT1331 231121 001 ISSUE01**

Manufacturer **Weidmüller Interface GmbH & Co. KG**

Address **Klingenbergstr. 26
32758 Detmold, Germany**

Object of the declaration **SAK – Series / Feed-through terminal blocks**

☒ Continued on page 2

The manufacturer attests, in sole-responsibility, that the object of the declaration described above is in conformity with the essential requirements of directive(s):

	Directive	
The Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 Marking (Equipment Group, Category, Atmosphere)	SI 2016/1107	SI2019/696(Schedule25) SI 2020/1460

References to the relevant BSEN or EN designated standards used, or references to the specifications, in relation to which conformity is declared:

EN IEC 60079-0:2018
EN IEC 60079-7:2015/A1:2018

Issued certificates from Approved Bodies

Approved Body (name, address and number)	Description of intervention	Certificate
ExVeritas, Units 16-18, Abenbury Way, Wrexham Industrial Estate, Wrexham, United Kingdom LL13 9UZ. Approved Body # 2585	Surveillance of production process (UKCA Ex)	ExVeritas 21UKQAN0176
Dekra Certification UK Ltd; Stokenchurch House, Oxford Road, Stokenchurch, HP14 3SX Approved Body # 8505	Surveillance of production process (UKCA Ex)	DEKRA 21UKQANxxxx
TUV Rheinland UK Ltd Friars Gate (Third Floor), 1011 Stratford Road, Shirley, Solihull, B90 4BN Approved Body # 2571	UKEx-Type Examination UKCA	TÜV 21 UKEX 7051 U

Detmold, 14.03.2022

Ort, Datum / place, date

Rechtsverbindliche Unterschrift / legally binding signature

Name und Funktion / name and function

Arnd Schepmann, Business Unit Leiter Terminals

This declaration certifies compliance with the indicated directive but no warranty of properties. The safety instructions of the accompanying product documentation shall be observe.

UK Attestation of Conformity

Document No.

UKCA DE PT1331 231121 001 ISSUE01

Object of the declaration

SAK 2.5	0279660001
SAK 2.5 BL	0279680001
SAK 2.5/10	0279860001
SAK 4	0128360001
SAK 4 BL	0128380001
SAK 4/35 OR	0443660001
SAK 4/35 SW	0443660001
SAK 4/35 WS	0443660001
SAK 4/35 GR	0443660001
SAK 4/35 GE	0443660001
SAK 4/35 BR	0443660001
SAK 4/35 RT	0443660001
SAK 4/35 BL	0443660001
SAK 4/35	0443660001
SAK 6N	0193260001
SAK 6N BL	0193280001
SAK 6/35 PA/BL	0380580001
SAK 6/35 PA	0380560001
SAK 10	0110060001
SAK 10 BL	0110080001
SAK 10/35	0443760001
SAK 10/35 BL	0443780001
SAK 16	0271060001
SAK 16 BL	0271080001
SAK 16/35 PA	0380660001
SAK 16/35 PA/BL	0380680001
SAK 35	0303560001
SAK 35 BL	0303580001
SAK 35/35	0380760001
SAK 35/35 BL	0380780001
SAK 35/35 IK	0582460001
SAK 2,5/35	0380460001
SAK 2.5/35 BL	0380480001
SAK 2.5/35 SW	2566510001
SAK 2.5/35 WS	2572380001
SAK 2.5/35 RT	2566530001
SAK 2.5/35 DBL	2566540001
SAK 2.5/35 OR	2566460001
SAK 2.5/35 GN	2572440001
SAK 2.5/35 BR	2566520001
SAK 2.5/35 GE	2572420001
SAK 2.5/35	2572430001
SAK 2.5/35	0380460001
SAK 2.5/35 BL	0380480001
SAK 2.5/35 SW	2566510001