



中国国家强制性产品认证证书



证书编号: 2023322313005498

认证委托人名称: Weidmüller Interface GmbH & Co. KG
认证委托人地址: Klingenbergstraße 26, 32758 Detmold, Germany
生产者名称: Weidmüller Interface GmbH & Co. KG
生产者地址: Klingenbergstraße 26, 32758 Detmold, Germany
生产企业名称: 魏德米勒电联接(苏州)有限公司
企业地址: 江苏省苏州高新区石林路58号
产品名称: 接线端子
系列、规格、型号: W2C系列, W2T系列
标准: GB/T 3836.1-2021、GB/T 3836.3-2021

认证模式: 型式试验+初始工厂检查+获证后监督

上述产品符合 CNCA-C23-01:2019 《强制性产品认证实施规则 防爆电气》的要求, 特发此证。
产品相关信息详见附件。

发证日期: 2023年08月30日

有效期至: 2028年08月29日

首次发证日期: 2023年08月30日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



批准:



上海仪器仪表自控系统检验测试所有限公司



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION



CERTIFICATE NO: 2023322313005498

APPLICANT: Weidmüller Interface GmbH & Co. KG
ADDRESS: Klingenbergstraße 26, 32758 Detmold, Germany
MANUFACTURER: Weidmüller Interface GmbH & Co. KG
ADDRESS: Klingenbergstraße 26, 32758 Detmold, Germany
FACTORY: Weidmüller Interface (Suzhou) Co. Ltd.
ADDRESS: Shilin Road No.58, SND, Suzhou, Jiangsu, P.R.China

PRODUCT: Terminals
SERIES,SPECIFICATION,MODEL: W2C Series, W2T Series
STANDARDS: GB/T 3836.1-2021、GB/T 3836.3-2021

Type of Certification: Type test + Initial inspection + Surveillance inspection

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification (REFNO. CNCA-C23-01:2019).
Refer to the attachment for detailed information.

Valid from: August 30, 2023

Valid until: August 29, 2028

Date of original certification: August 30, 2023

The validity of this certificate is subject to positive result of the periodic surveillance by issuing certification body until the expiry date.

This certificate is available through CNCA's website: www.cnca.gov.cn



APPROVAL:

Guo AiHua



Shanghai Inspection and Testing Institute of Instruments and Automation Systems Co., Ltd.

<http://www.sitias.com.cn>

Building 9, 103 Cao Bao Road, Shanghai 200233, China

Tel: +86 21 64510844

S 0008113



中国国家强制性产品认证证书



证书编号: 2023322313005498

附 件

产品名称: 接线端子

型号规格: W2C系列, W2T系列 (具体型号规格见电气参数表)

防爆标志: Ex ec IIC Gc

电气参数:

产品型号	电压(V)	电流(A)
W2C 4 DT*	550	26
W2C 4 DT * STB		23.5 (带 ZQV)
W2C 4 DT-PE*		
W2C 4 DT-PE * STB		
W2C 4 FS*	550 (基本模块) 250 (带保险丝)	6.3
W2C 4 FS-PE*		
W2C 4 FS * STB		
W2C 4 FS-PE * STB		
W2C 4 FS 10-36V*	10-36	6.3
W2C 4 FS-PE 10-36V*		
W2C 4 FS 10-36V * STB		
W2C 4 FS-PE 10-36V * STB		
W2C 4 FS 30-70V*	30-70	6.3
W2C 4 FS-PE 30-70V*		
W2C 4 FS 30-70V * STB		
W2C 4 FS-PE 30-70V * STB		
W2C 4 FS 60-150V*	60-150	6.3
W2C 4 FS-PE 60-150V*		

批 准:



上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书



证书编号: 2023322313005498

附 件

W2C 4 FS 60-150V * STB		
W2C 4 FS-PE 60-150V * STB		
W2C 4 FS 100-250V*	100-250	6.3
W2C 4 FS-PE 100-250V*		
W2C 4 FS 100-250V * STB		
W2C 4 FS-PE 100-250V * STB		
W2T 4 DT-FT*	550	23 (上层)
W2T 4 DT-FT-PE*		28 (下层)
W2T 4 DT-FT * STB		22 (上层带 ZQV)
W2T 4 DT-FT-PE * STB		24 (下层带 ZQV)
W2T 4 FS-FT*	550 (基本模块) 250 (带保险丝)	6.3
W2T 4 FS-FT-PE*		
W2T 4 FS-FT * STB		
W2T 4 FS-FT-PE * STB		
W2T 4 FS-FT 10-36V*	10-36	6.3
W2T 4 FS-FT-PE 10-36V*		
W2T 4 FS-FT 10-36V * STB		
W2T 4 FS-FT-PE 10-36V * STB		
W2T 4 FS-FT 30-70V*	30-70	6.3
W2T 4 FS-FT-PE 30-70V*		
W2T 4 FS-FT 30-70V * STB		
W2T 4 FS-FT-PE 30-70V * STB		
W2T 4 FS-FT 60-150V*	60-150	6.3
W2T 4 FS-FT-PE 60-150V*		
W2T 4 FS-FT 60-150V * STB		

批 准:



上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书



证书编号: 2023322313005498

附 件

W2T 4 FS-FT-PE 60-150V * STB		
W2T 4 FS-FT 100-250V*	100-250	6.3
W2T 4 FS-FT-PE 100-250V*		
W2T 4 FS-FT 100-250V * STB		
W2T 4 FS-FT-PE 100-250V * STB		
选配附件:		
挡板 WEP 2C 4*, WEP 2T 4*	/	/
固定块 WEW 35/2 SW*		
导轨 TS 35/...		
横联件 ZQV 4N/(1)*		

注: (1)表示横联的位数; *表示所有颜色, 与防爆性能无关。

相关报告编号: 2023S17402-012509

使用条件:

特殊(限制)使用条件:

- 1) 使用工作温度: $-60^{\circ}\text{C} \sim +130^{\circ}\text{C}$ 。
- 2) 对于爆炸性气体环境, 端子应安装在经认证的防护等级为 IP54 的外壳内。对于可燃性粉尘环境, 端子应安装在经认证的防爆型式为“t”的外壳内(符合 GB/T 3836.31)。
- 3) 当与其他系列和尺寸接线端子接合使用, 或者使用其他附件时, 则应满足合适的爬电距离和电气间隙。
- 4) 外壳的结构应能阻挡所有的日光和紫外线影响接线端子。
- 5) 关于产品的使用, 必须遵守制造商的说明。
- 6) 对于横联件, 必须考虑端子间的电流和电阻。有关产品的详细信息, 请参阅“安装人员须知 NTI”。
- 7) 保险丝座应始终完全闭合, 通电时请勿拆卸或更换保险丝。

批 准:



上海仪器仪表自控系统检验测试所有限公司



中国国家强制性产品认证证书



证书编号: 2023322313005498

附 件

- 8) 如果使用的导线横截面小于额定导线横截面, 则应在成套设备证书中说明相应的较低电流。
- 9) 应对温度组别 T6...T1 进行热评估。有关最高使用环境温度范围, 请参阅“安装人员须知 NTI”。

批 准:



上海仪器仪表自控系统检验测试所有限公司