

## 8000124332 PV combiner box thermal report

### PV 220S0F3CXXV000TXPX15PWW

#### INPUT DATA


Enclosure model	847 x 636 x 300 mm
Number of MPPT	1
Switch-disconnector model (per MPPT)	400A 1500V
Maximum current (per MPPT)	350 A
Number of inputs (per MPPT)	20
Fuse-link model	30A gPV 1500V 10x85mm
Number of monitoring devices (per MPPT)	0
Type of mounting	Against wall, all other sides detached
Maximum allowed internal temperature	70 °C
Combined inputs	1
Height (A)	847 mm
Width (B)	636 mm
Depth (C)	300 mm
Effective cooling surface Ae of the enclosure	1.48 m <sup>2</sup>

#### RESULTS

Ambient temperature (no direct sunlight)	35 °C
Rated current per input at 35°C	17.50 A
Power dissipated by components (except wiring)	90 W
Power dissipated by wiring	34 W
Total dissipated power	124 W
Temperature rise, mid height	20 °C
Temperature rise, top	25 °C
Internal temperature, top	60 °C

#### CURRENT RATINGS

At 35°C	17.50 A
At 40°C	17.50 A
At 45°C	17.50 A
At 50°C	14.44 A



#### NOTES

Thermal report based on IEC TR 60890 ed2.0

Thermal report does not include the direct sunlight effects