





Technical drawing of a cable gland (PG9) showing dimensions and components. The drawing includes a side view and a top view. The side view shows the gland with a cable passing through it. The top view shows the gland with a cable passing through it. The dimensions are as follows:

- PG9 (Gland size)
- M12x1 (Thread size)
- 18 (Height of the gland body)
- 20,5 (Total height of the gland)
- O-Ring FPM (Top O-ring material)
- SW 19 (Hex key size for the lock nut)
- O-Ring NBR (Bottom O-ring material)
- Ø0,8 (Cable diameter)
- D2 (Cable outer diameter)
- D1 (Cable inner diameter)
- A (Arrow indicating direction of force or assembly)



Order no.:	Description:	Pole	Length L:	D1	D2
2421920000	SAIE-M12B-4-H5.5TL-PG9	4	5,5mm	Ø5,0	Ø1,6
2421980000	SAIE-M12B-5-H5.5TL-PG9	5			
2422040000	SAIE-M12B-8-H5.5TL-PG9	8		Ø5,5	Ø1,4
2421950000	SAIE-M12B-4-H12TL-PG9	4	12mm	Ø5,0	Ø1,6
2422010000	SAIE-M12B-5-H12TL-PG9	5			
2422070000	SAIE-M12B-8-H12TL-PG9	8		Ø5,5	Ø1,4