

INSTALLATION INSTRUCTIONS
& CONDITIONS FOR SAFE USE



II 2 GD

Ex eb IIC Gb

Modular TERMINAL Blocks: W- Series

DEMKO 14 ATEX1338 U

IECEX ULD 14.0005U

UL21UKEX2114U

Standards:

EN IEC 60079-0:2018 and EN 60079-7:2015, EN IEC 60079-7:2015/A1:2018
IEC 60079-0: 7th Edition and IEC 60079-7: 5.1th Edition

Modular Terminal Blocks: WDU/WPE

Version:	WDU 120/150*	Order No 1024500000
----------	--------------	------------------------

in conjunction with:	WPE 120/150*	Order No 1846040000
----------------------	--------------	------------------------

Accessories:	Type	Order No
End bracketed	WEW 35/1 V0 GF... *	
Terminal rail	TS 35/... acc.to DIN EN 60715	

Cross-connection	Screwable*	Order No
	WQV 120/2	1063300000
	WQV 120/3	1063400000

Insulation material:

- Type	Wemid
- Tracking resistance (A) to IEC 60112	CTI ≥ 600
- Flamability class to UL 94	V0
- Operating temperature range	-60°C...+110°C (insulating material limit)
- Ambient temperature range	-60°C...+40°C (for T6 applications)
- Ambient temperature range	-60°C...+55°C (for T5 applications)
- Ambient temperature range	-60°C...+70°C (for T4 applications)

* in all colours and optional with hexagon and six lobe drive

Technical data according to IEC/EN 60079-7 (increased safety "eb"):


	WDU 120/150	WPE 120/150
- Rated voltage	1100 V	
- Rated current	264 A / ΔT 40 K	
- Temperature rise with rated current	32,7 K / 264 A	
- Rated current with WQV	265 A / ΔT 40 K	
- Contact resistance with rated conductor, 120 mm ²	0,04 m Ω	0,07 m Ω
- Rated conductor cross section	150 mm ²	120 mm ²
- Conductor cross section solid	16 mm ²	16 mm ²
- Conductor cross section stranded	35 - 150 mm ²	35 - 150 mm ²
- Conductor cross section flexible	35 - 150 mm ²	35 - 150 mm ²
- cross section, American Wire Gauge	2 - 00000 AWG	2 - 00000 AWG
- conductor cross section flexible with ferrule acc. to DIN 46228 part 1 + 4	35 - 150 mm ²	35 - 150 mm ²
- 2 conductors with same cross-section	35 - 70 mm ²	--
- Tightening torque range, terminal screw	10 - 20 Nm	10 - 20 Nm
- Tightening torque range, fixing screw		3,0 - 6,0 Nm
- Tightening torque range for WQV...	2,0 - 3,0 Nm	
- Stripping length	35 mm	35 mm

IECEx / ATEX / UKCA Terminal and Cross-Connector Arrangements:

Max voltage data according to IEC/EN 60079-7 in conjunction with protective conductor terminal blocks of the WPE-Series, (increased safety "eb"):


Application Case

A Continuous




1100 V

B Adjacent



1100 V

E Next to a protective conductor terminal (earth) without a partition plate



1100 V

Information for further cross-connector arrangements will be provided on request.

Note:

If smaller cross sections than the rated cross section are used, the belonging lower current has to be laid down in the IECEx/EC-Type Examination Certificate of the complete apparatus.

Mounting instructions:

The WDU/WPE series is suitable for application in enclosures in atmospheres with flammable gases or combustible dust. For use in flammable gases these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-7. For use in combustible dust these enclosures must satisfy the requirements according to IEC/EN60079-0 and IEC/EN60079-31.

Regarding the use of accessories the instructions of the manufacturer must be followed.

Schedule of Limitations:

The WDU/WPE terminals are suitable for use in enclosures in atmospheres with flammable gases or combustible dust. For flammable gases these enclosures must satisfy the requirements according to DIN/EN 60079-0 and DIN/EN 60079-7. For combustible dust the enclosure must satisfy the requirements according to DIN/EN 60079-0 and DIN/EN 60079-31.

The terminal blocks shall be placed inside a suitable IECEx/ATEX/UKCA certified IP54 enclosure for gas atmosphere. For dust atmosphere the terminal blocks shall be mounted inside a suitable IECEx/ATEX/UKCA certified 't' enclosure (IEC/EN60079-31).

Under normal operating conditions the temperature rise of the terminal blocks is maximum 40 K, measured at the maximum permitted rated current. Due to the above mentioned, the terminal blocks may be used in apparatus of temperature classes T6..T1 as long as the terminal block ambient temperature range is not exceeded. No part of terminal block must exceed 110 °C under any condition.

T6 (- 60°C ... +40 °C)

T5 (- 60°C ... +55 °C)

T4 (- 60°C ... +70 °C)

When using the type WDU/WPE especially with other terminal blocks series or sizes or accessories the requirements for clearance and creepage distances according to DIN/EN 60079-7 must be observed. Regarding the use of covers, cross-connectors and end brackets the instructions of the manufacturer must be followed.

For cross connection accessories, current rating, resistance across the terminal and torque values please refer to the table under "technical data" above.

When using ferrules for flexible conductors, it must be ensured that the test requirements of DIN 46228-1 and DIN 46228-4 are complied with. Therefore we recommend the use of the appropriate Weidmüller crimping tools. The length of the copper ferrule must correspond to the specified stripping length.

The terminal can be used with either one or two wires into either side of the terminal. When two wires are used they must be of the same type, and of equal sizes. No other wire sizes or types than the ones specified in instructions must be used. The terminal blocks must either be mounted next to another block of the same type and size or with an end plate.

If smaller conductor cross sections than the rated conductor cross sections are used, then the corresponding lower current shall be stated in the Certificate of the complete apparatus.

Unused terminals shall be tightened.

Essential Health and Safety Requirements:

Concerning ESRs this Schedule verifies compliance with the Annex II of ATEX / Schedule 1 of UKCA directive and Equipment and Protective Systems Intended for Use in Potentially Explosive Atmospheres Regulations 2016 only. By placing the product on the market, the manufacturer declares compliance with other relevant Directives, and all other safety related requirements including those of Annex II / Schedule 1 of these Directives.