





Allgemeingültige Kundenzeichnung, aktueller Stand nur auf Anfrage
General customer drawing, topical version only if required

Shown: MHS 7.5/04 V T3



Hole pattern

For the mounting of PCBs, it should be noted that the rated data relates only to the PCB components alone.


The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to IEC 60664 / VDE 0110.

The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller PCB components are tested according to the DIN EN 61984 or to the DIN EN 60947-7-4 standard, and are valid for its field of application.

Provided that the components are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

Further dim. & info. see data sheet



M 1/1

8	52.50	2.067
7	45.00	1.772
6	37.50	1.476
5	30.00	1.181
4	22.50	0.886
3	15.00	0.591
2	7.50	0.295
n Poles	L1 [mm]	L1 [inch]

RoHS COMPLIANT	First Issue Date 16.04.2021	Prim PLM Part No.: .		Prim ERP Part No.: .
		Max. nos.		Modification
		Date	Name	Weidmüller
		Drawn	16.04.2021 Tauber-Reglin,	
		Responsible		
Scale: 3/1	Size: A3	Approved	29.04.2021 Sapina, Svetos	
Drawings Assembly				Product file:

MHS 7S/... V T3 ...

0

0

0