



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Ex COMPONENT CERTIFICATE

Certificate No.: **IECEx TUR 16.0046U**

Page 1 of 4

Certificate history:

Status: **Current**

Issue No: 3

Issue 2 (2018-02-28)

Issue 1 (2017-05-03)

Issue 0 (2017-01-19)

Date of Issue: **2021-05-27**

Applicant: **Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
Detmold 32758
Germany

Ex Component: **Terminal block type APGTB ***

This component is NOT intended to be used alone and requires additional consideration when incorporated into other equipment or systems for use in explosive atmospheres (refer to IEC 60079-0).

Type of Protection: **Ex e**

Marking: **Ex ec IIC Gc**

Approved for issue on behalf of the IECEx
Certification Body:


Christian Mehrhoff

Position:

Assigned certifier

Signature:
(for printed version)

Date:


2021-05-27

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.



Certificate issued by:

TUV Rheinland Industrie Service GmbH
Am Grauen Stein
51105 Cologne
Germany





IECEx Certificate of Conformity

Certificate No.: **IECEx TUR 16.0046U**

Page 2 of 4

Date of issue: 2021-05-27

Issue No: 3

Manufacturer: **Weidmüller Interface GmbH & Co. KG**
Klingenbergstrasse 26
Detmold 32758
Germany

Additional
manufacturing
locations:

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

STANDARDS :

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

IEC 60079-0:2017 Explosive atmospheres - Part 0: Equipment - General requirements
Edition:7.0

IEC 60079-7:2017 Explosive atmospheres - Part 7: Equipment protection by increased safety "e"
Edition:5.1

This Certificate **does not** indicate compliance with safety and performance requirements other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

[DE/TUR/ExTR16.0046/03](#)

Quality Assessment Report:

[NL/DEK/QAR12.0052/07](#)



IECEx Certificate of Conformity

Certificate No.: **IECEx TUR 16.0046U**

Page 3 of 4

Date of issue: 2021-05-27

Issue No: 3

Ex Component(s) covered by this certificate is described below:

The terminal block series APGTB * is for the connection of copper conductors in enclosures. The type of protection is increased safety, "e" - Level of Protection "ec" (EPL "Gc").

This assessment covers the types

APGTB 2.5 2T 4C/2*, APGTB 2.5 2T FT-PE 4C/2*, APGTB 2.5 2T PE 4C/2*, APGTB 2.5 2T VL 4C/2*, APGTB 2.5 FT 2C/1*, APGTB 2.5 PE 2C/1*, APGTB 2.5 FT 3C/1*, APGTB 2.5 PE 3C/1*, APGTB 2.5 FT 4C/2*, APGTB 2.5 PE 4C/2*, APGTB 1.5 FT 2C/1*, APGTB 1.5 PE 2C/1*, APGTB 1.5 FT 3C/1*, APGTB 1.5 PE 3C/1*, APGTB 1.5 FT 4C/2*, APGTB 1.5 PE 4C/2*, APGTB 1.5 2T 4C/2*, APGTB 1.5 2T FT-PE 4C/2*, APGTB 1.5 2T PE 4C/2*, APGTB 1.5 2T VL 4C/2*

where * is not Ex relevant.

Optional accessories:

End plate: AEP*

End bracket: AEB 35 SC/1

Terminal rail: TS 35/... acc.to DIN EN 60715

In combination with: APG 2.5/1*, APG 2.5/2*, APG 2.5/3*, APG 2.5/4*, APG 2.5/5*, APG 2.5/6*, APG 2.5/7*, APG 2.5/8*, APG 2.5/9*, APG 2.5/10*, APG 2.5/L*, APG 2.5/MI*, APG 2.5/R*, APG 2.5/5-3BG-BL-GNYL, APG 2.5/4-3BG-GNYL, APG 2.5/3-BG-BL-GNYL

Cross connection pluggable: ZQV ** / **

Looking clip: ZVR ZP*, APGLE *

Technical data:

Operating temperature: -60°C....+130°C

For other technical data refer to the "Installation instructions & condition of safe use" for each type of terminal.

SCHEDULE OF LIMITATIONS:

1. The terminal blocks shall be placed inside a suitable IECEx certified IP54 enclosure for gas atmosphere. For dust atmosphere the terminal blocks shall be mounted inside a suitable IECEx certified 't' enclosure (IEC 60079-31).
2. The enclosure shall be constructed to block all sun and UV light from affecting the terminal blocks.
3. A thermal assessment for the classification into the temperature classes T6.....T1 shall be performed. No part of terminal block must exceed +130 °C under any condition.
4. For cross connection accessories the current ratings and the resistances across the terminals have to be considered. Please refer to the table under "types & electrical rating" above.
5. Manually cut jumper and jumpers with blank ends shall not be used.
6. The insulation material of the conductors shall meet the temperature requirements



IECEx Certificate of Conformity

Certificate No.: **IECEx TUR 16.0046U**

Page 4 of 4

Date of issue: **2021-05-27**

Issue No: 3

DETAILS OF CERTIFICATE CHANGES (for issues 1 and above)

- Standard update.
- Address change of applicant and manufacturer.