

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Specification Text short:

Manufacturer:	Weidmüller
Brand:	Klippon®
Type:	Terminal box, junction box, distribution box
Enclosure range:	Klippon K
Material:	Aluminium AlSi12
Lid:	4x captive fixing screws (Torx-Slot)
Ambient temperatures:	-40 °C ≤ Tamb ≤ +85 °C (DIN EN 62208), including aging cycles


Specification Text long:

Manufacturer:	Weidmüller
Brand:	Klippon®
Type:	Terminal box, junction box, distribution box
Enclosure range:	Klippon K
Description:	Klippon K0 RAL7001
Article number:	9529090000
Material:	Aluminium AlSi12
Manufacturing process:	Die-cast aluminum.
Wall thickness:	Enclosure base ≥ 3 mm, Draft angle 1 to 2 ° / lid 2 mm
IP / NEMA Rating:	IP66, IP 67, IP 68 (EN 62208, DIN EN 60529) / NEMA 4, 4X (UL 50E, CSA C22.2)
Surface:	Powder coated (RAL 7001)
Dimensions (H x W x D):	45 mm x 50 mm x 30 mm
Lid:	4x captive fixing screws (Torx-Slot)
Sealing for lid:	Single (non-jointed) chloropren O-ring with compression control, to prevent damage to the sealing gasket
Earth bolt:	Internal: Srew connection / External: As option
Enclosure attachment:	4x captive fixing screws (Torx-Slot)
Ambient temperatures:	-40 °C ≤ Tamb ≤ +85 °C (DIN EN 62208)
Impact resistance:	IK 09 (10 J) (DIN EN 50102)

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Klippon K0



Options:

Label fixing sets:

Stainless steel V4A / 316L / 1.4404, screwed or fixed by rivets. Punched silicon gasket with compression control for the label and its silicon gasket, to ensure the IP rating.

Mounting plates:

Earth bolt:

Internal / external: M10 of stainless steel V4A / 316L / 1.4404 or M10 of brass or M6 of stainless steel V4A / 316L / 1.4404 or M6 of brass

Assembly of terminals:

All terminal blocks of type Klippon® Connect. All DIN rails vertical mounting, horizontal mounting as option. Terminal marker horizontal. Hazardous areas: All terminals for intrinsically safe circuits are colored blue, for non-intrinsically safe circuits are colored dark beige. On request: Assembly with control stations (switches, push buttons, lights, indicators).

Certifications:

For assembled resp. empty enclosures
cULus
Russian Maritime Register of Shipping

Specification Text - Enclosure, Aluminium

45 mm x 50 mm x 30 mm ... 230 mm x 280 mm x 111 mm (Hight x Width x Depth)

Weidmüller Interface GmbH & Co. KG

Postfach 3030

32720 Detmold

Klingenbergstraße 16

32758 Detmold

Phone +49 (0) 5231 14-0

Fax +49 (0) 5231 14-292083

E-Mail info@weidmueller.com

Internet www.weidmueller.com

You can find your local contact
on the internet at:

www.weidmueller.com/countries