



IECEx Certificate of Conformity

INTERNATIONAL ELECTROTECHNICAL COMMISSION IEC Certification System for Explosive Atmospheres

for rules and details of the IECEx Scheme visit www.iecex.com

Ex COMPONENT CERTIFICATE

Certificate No.: **IECEx TUR 16.0036U** Page 1 of 4

Status: **Current** Issue No: 9

Date of Issue: 2021-10-20

Applicant: **Weidmüller Interface GmbH & Co. KG**
Klingenbergsstrasse 26
Detmold 32758
Germany

Ex Component: **Terminals type A* Series**

Certificate history:

Issue 8 (2021-07-26)
Issue 7 (2020-10-02)
Issue 6 (2019-11-14)
Issue 5 (2019-07-09)
Issue 4 (2019-02-28)
Issue 3 (2018-05-28)
Issue 2 (2017-11-08)
Issue 1 (2017-07-27)
Issue 0 (2017-02-16)

This component is NOT intended to be used alone and requires additional consideration when incorporated into other equipment or systems for use in explosive atmospheres (refer to IEC 60079-0).

Type of Protection: **Ex eb**

Marking: **Ex eb IIC Gb**


Approved for issue on behalf of the IECEx
Certification Body:

Christian Mehrhoff

Position:

Assigned certifier

Signature:
(for printed version)


2021-10-20

Date:

1. This certificate and schedule may only be reproduced in full.
2. This certificate is not transferable and remains the property of the issuing body.
3. The Status and authenticity of this certificate may be verified by visiting www.iecex.com or use of this QR Code.



Certificate issued by:

TÜV Rheinland Industrie Service GmbH
Am Grauen Stein
51105 Cologne
Germany





IECEx Certificate of Conformity

Certificate No.: **IECEx TUR 16.0036U**

Page 2 of 4

Date of issue: **2021-10-20**

Issue No: 9

Manufacturer: **Weidmüller Interface GmbH & Co. KG**
Klingenbergsstrasse 26
Detmold 32758
Germany

Additional
manufacturing
locations:

This certificate is issued as verification that a sample(s), representative of production, was assessed and tested and found to comply with the IEC Standard list below and that the manufacturer's quality system, relating to the Ex products covered by this certificate, was assessed and found to comply with the IECEx Quality system requirements. This certificate is granted subject to the conditions as set out in IECEx Scheme Rules, IECEx 02 and Operational Documents as amended

STANDARDS :

The equipment and any acceptable variations to it specified in the schedule of this certificate and the identified documents, was found to comply with the following standards

IEC 60079-0:2017 Explosive atmospheres - Part 0: Equipment - General requirements
Edition:7.0

IEC 60079-7:2017 Explosive atmospheres - Part 7: Equipment protection by increased safety "e"
Edition:5.1

This Certificate **does not** indicate compliance with safety and performance requirements
other than those expressly included in the Standards listed above.

TEST & ASSESSMENT REPORTS:

A sample(s) of the equipment listed has successfully met the examination and test requirements as recorded in:

Test Report:

[DE/TUR/ExTR16.0036/09](#)

Quality Assessment Report:

[NL/DEK/QAR12.0052/07](#)



IECEx Certificate of Conformity

Certificate No.: **IECEx TUR 16.0036U**

Page 3 of 4

Date of issue: **2021-10-20**

Issue No: 9

Ex Component(s) covered by this certificate is described below:

The Feed-through and protective conductor terminals of the A-series are suitable for use in enclosures in atmospheres with flammable gases or combustible dust.

Technical data: See manufacturer's installation instructions of each single terminal type for details.

More information see attachment.

SCHEDULE OF LIMITATIONS:

1. The Feed-through terminals and PE terminals of the A-series are suitable for use in enclosures in atmospheres with flammable gases or combustible dust. For flammable gases these enclosures must satisfy the requirements according to IEC 60079-0 and IEC 60079-7. For combustible dust the enclosure must satisfy the requirements according to IEC 60079-0 and IEC 60079-31.
2. The enclosure shall be constructed to block all sun and UV light from affecting the terminal blocks. The terminal blocks shall be placed inside a suitable certified IP54 enclosure in type of protection "e" for gas atmosphere. For dust atmosphere the terminal blocks shall be mounted inside a suitable certified enclosure (IEC60079-31) in type of protection "t".
3. Under normal operating conditions the temperature rise of the terminal blocks is maximum 40 K, measured at the maximum permitted rated current. Due to the above mentioned, the terminal blocks may be used in apparatus of temperature classes T6..T1 as long as the terminal block ambient temperature range is not exceeded. No part of terminal block must exceed 110 °C under any condition.

T6 (- 60°C ... +40 °C)

T5 (- 60°C ... +55 °C)

T4 (- 60°C ... +70 °C)

4. When using the types A*C ** and A*C ** PE especially with other terminal blocks series or sizes or accessories the requirements for clearance and creepage distances according to table 1 of IEC 60079-7 must be observed. Regarding the use of covers, cross-connectors and end brackets the instructions of the manufacturer must be followed.
5. For cross connection accessories, current rating, resistance across the terminal please refer to the table under "Technical data" of the "Notice to Installers".
6. No other wire sizes or types than the ones specified in instructions must be used. The terminal blocks must either be mounted next to another block of the same type and size or with an end plate.
7. If smaller conductor cross sections than the rated conductor cross sections are used, then the corresponding lower current shall be stated in the Certificate of the complete apparatus.
8. Manually cut cross connections and cross connections with blank ends (ZQV's ≥ 20 poles) shall not be used.



IECEx Certificate of Conformity

Certificate No.: **IECEx TUR 16.0036U**

Page 4 of 4

Date of issue: 2021-10-20

Issue No: 9

DETAILS OF CERTIFICATE CHANGES (for issues 1 and above)

- Integration of terminals A2C 50/75 and A2C 95/120.

Annex:

[IECEx TUR 16.0036U_09_attachment.pdf](#)



Device: Terminal
Type: A* Series

Manufacturer: Weidmüller Interface GmbH & Co. KG

Address: Klingenbergsstraße 26,
32758 Detmold, Germany

Equipment and type

Terminal type A* Series

With type designations as follows:

A2C 1.5	A2T 2.5	A2C 10	A2T 4 FT - PE
A2C 1.5 PE	A2T 2.5 FT-PE	A2C 10 PE	A2T 4 VL
A4C 1.5	A2T 2.5 VL	A3C 10	A2T 4 PE
A4C 1.5 PE	A2T 2.5 PE	A3C 10 PE	A2C 35
A2C 2.5	ALO 6,	A2T 1.5	A2C 35-DM
A2C 2.5 PE	A3C 1.5	A2T 1.5 FT-PE	A2C 35 PE
A3C 2.5	A3C 1.5 PE	A2T 1.5 VL	A2C 35 3FT-N-PE
A3C 2.5 PE	A3C 4	A2T 1.5 PE	A2C 35 3FT-N
A4C 2.5	A3C 4 PE	A2C 16	A2C 35 3FT-PE
A4C 2.5 PE	A2C 2.5 /DT/FS	A2C 16 PE	A2C 35 3FT
A2C 4	A2C 2.5 PE/DT/FS	A3C 16	A2C 35 3FT-FE
A2C 4 PE	A3T 2.5	A3C 16 PE	A2C 35 3FT-N-FE
A4C 4	A3T 2.5 PE	ALO 16	A2C 35 3FT-N-FE-DM
A4C 4 PE	A3T 2.5 FT-FT-PE	A2T 2.5 3C	A2C 35 3FT-N-DM
A2C 6	A3T 2.5 N-FT-PE	A2T 2.5 3C FT-PE	A2C 35 3FT-FE-DM
A2C 6 PE	A3T 2.5 VL	A2T 2.5 3C VL	A2C 35 3FT-DM
A3C 6	AMC 2.5	A2T 2.5 3C PE	A2C 50/75
A3C 6 PE	AMC 2.5 800V	A2T 4	A2C 95/120

Optional accessories:

End plate:	AEP ***.**
End bracket:	AEB 35 SC/1*
	ZEW 35*
Terminal rail:	TS 35/** acc.to DIN EN 60715
Cross connection:	pluggable:ZQV *.*N/**

General product information

The Feed-through and protective conductor terminals of the A-series are suitable for use in enclosures in atmospheres with flammable gases or combustible dust.

Technical data

Operating temperature ranges:	-60°C up to +110°C
T6	-60°C up to +40 °C
T5	-60°C up to +55 °C
T4	-60°C up to +70 °C

See manufacturer's installation instructions of each single terminal type for details.