

CERTIFICATE

Issued to:
Applicant:
Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16
32758 Detmold, Germany

Licensee:
Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16
32758 Detmold, Germany

Product : Terminal blocks for copper conductors
Trade name(s) : Weidmüller
Type(s)/model(s) : Series DK 4

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 60947-7-1:2009
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 900119


DEKRA hereby grants the right to use the KEMA-KEUR certification mark.

The KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the KEMA-KEUR certification agreement and under the conditions of the KEMA-KEUR certification agreement.

This certificate is issued on 12 December 2018 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 71-106554

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



K. Lin
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: Terminal blocks for copper conductors
Trade name(s)	: Weidmüller
Type(s)/model(s)	: DK 4, DK 4/35, DK 4Q/32, DK 4Q/35, DK 4QV/32 and DK 4QV/35
Conventional free air thermal current	: 32 A
Rated insulation voltage	: 400 V
Rated impulse withstand voltage	: 6 kV
Rated connecting capacity	: 0,5 mm ² - 6 mm ² rigid or flexible
Rated cross section	: 4 mm ²
Tightening torque	: 0,5 - 0,8 Nm
Pollution degree	: 3
Stripping length	: 8 mm

Product data – type DK 4

Description	: Feed-through, double-level terminal block
Mounting rail	: G-type rail 32 mm

Product data – type DK 4/35

Description	: Feed-through, double-level terminal block
Mounting rail	: Top hat rail 35 mm

Product data – type DK 4Q/32

Description	: Feed-through, double-level terminal block lower level also bridgeable
Mounting rail	: G-type rail 32 mm

Product data – type DK 4Q/35

Description	: Feed-through, double-level terminal block lower level also bridgeable
Mounting rail	: Top hat rail 35 mm

Product data – type DK 4QV/32

Description	: Feed-through, double-level terminal block lower level also bridgeable and vertically cross-connected
Mounting rail	: G-type rail 32 mm

Product data – type DK 4QV/35

Description	: Feed-through, double-level terminal block lower level also bridgeable and vertically cross-connected
Mounting rail	: Top hat rail 35 mm

TESTS**Test requirements**

EN 60947-7-1:2009

Test result

The test results are laid down in DEKRA test file 222855000.

Conclusion

The examination proved that all requirements were met.

Factory location

Weidmüller Interface GmbH & Co. KG
Klingenbergstrasse 16
32758 Detmold, Germany